








FCIconnect.com

Copyright FCI



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.PX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.PX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.PX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.PX00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6±0.15 mm.

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title			
E	ELX-I-22878	AB	2015/01/06	angles	linear		FEMALE CONNECTOR DELTA-D			
				0°±2'			STRAIGHT - SOLDER TYPE FOR PCB 2.4mm			
				dr	LELEON	1992/09/16		dwg no		sheet 1 of 1
				enr	ALIAS BABU	2015/01/06		C01-8646-0122		A3
				chr	MITHUN PAUL	2015/01/06		type		Product Customer Drawing
				app	BIJU K PAUL	2015/01/06				
sheet index	revision	E	1							