



NOTES:

1. MATERIALS AND FINISHES:
BODY - BRASS, TIN PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC-12.0 GHz
C. VSWR (RETURN LOSS): 1.22 (20dB)
D. D.W.V: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65°C TO +165°C

THIRD ANGLE PROJ.

REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	19-Apr-17	3463	RM



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°	MATERIAL	DRAWN	DATE	TITLE 75 OHM BNC P.C.MOUNT RECEPT. JACK		Amphenol RF www.amphenolrf.com	
	-	B. GREENBAUM	05-Apr-17				
	REFERENCE	ENGINEER	DATE				
	EAR# 7475	B. GREENBAUM	05-Apr-17	SCALE: 6.0:1.0		DRAWING NO. 31-70536-12G	
	EXP# --	APPROVED	DATE	SHEET 2 OF 2		ITEM NO. 31-70536-12G	
	CONFIGURATION LEVEL: In Work	S.HSIEH	19-Apr-17	DWG SIZE		REV	
	FINISH	CAD FILE		B		A	
						PART NO. 31-70536-12G	