



HONEYWELL PART NUMBER
11SM401-H58
PRODUCT CODE TWY0140

REV	DOCUMENT	CHANGED BY	CHECK
9	0038104	PK 23APR08	ASD



PLASTIC PLUNGER



NOTE -
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
2 PLATED TERMINALS WILL ACCEPT "AMP INC".058 DIA PIN RECEPTACLES.
3- DEAD BREAK CONDITIONS:
A- MAX AMOUNT PERMISSABLE - - -.0002 IN.

RELEASE NO.	PR - 4670
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± 0.030 0.015 0.005				DRAWN		VK		27 NOV 07		Honeywell							
OPERATING FORCE — — 3 1/2 OZ MAX		CONTACT ARRANGEMENT SPDT								CHECK		RJ		27 NOV 07									
RELEASE FORCE — — — — 1 OZ MIN		30 VOLTS DC RATING				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC													
DIFFERENTIAL TRAVEL — — — .001 MAX				SEA LEVEL												50,000 FT							
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE		3 AMP						2.5 AMP													
		RESISTIVE		5 AMP						5 AMP													
		MAXIMUM INRUSH 24 AMP				THIRD ANGLE PROJECTION 				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE		TYPE		DRAWING NAME				REV	
		APPROVALS		KEMA, CE						5A, 250V ~ T85 1E4				B		I		11SM401-H58				9	
				UL, CSA						5A, 250 VAC													