

FL SFP SX - Media module

2891754

<https://www.phoenixcontact.com/us/products/2891754>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Gigabit SFP module for transmission up to 1 km with a wavelength of 850 nm.

Product description

SFP module with a data transmission speed of 1000 Mbps, a wavelength of 850 nm, and a maximum transmission length of 1 km.

Your advantages

- MSA compliant

Commercial data

Item number	2891754
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN22
Product key	DNN613
Catalog page	Page 332 (C-6-2019)
GTIN	4046356166782
Weight per piece (including packing)	28.8 g
Weight per piece (excluding packing)	28.8 g
Customs tariff number	85176200
Country of origin	TW

FL SFP SX - Media module

2891754

<https://www.phoenixcontact.com/us/products/2891754>



Technical data

Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Housing material	Metal
------------------	-------

Mounting

Mounting type	Insert in SFP slot
---------------	--------------------

Interfaces

Ethernet FO

Connection method	LC
Transmission speed	1 Gbps
Transmit capacity, minimum	-9 dBm
Transmit capacity, maximum	-4 dBm
Minimum receiver sensitivity	-17 dBm
Maximum receiver sensitivity	-3 dBm
Transmission physics	multi-mode fiberglass
Transmission length	275 m (Fiberglass, 62.5/125 µm (OM1))
	550 m (Fiberglass, 50/125 µm (OM2))
	1000 m (Fiberglass, 50/125 µm (OM3))
	1000 m (Fiberglass, 50/125 µm (OM4))
Wavelength	850 nm
Signal LEDs	depending on the Factoryline device
No. of channels	1 (LC multi-mode)

Product properties

Product type	SFP module
Type	Factoryline devices with SFP slot
MTTF	667 Years (Telcordia SR-332, temperature factor at 40°C = 1, stress factor at 50% = 1, environmental factor = 1)
Format	SFP (Small Form-factor Pluggable)

Signaling

Status display	via a Factoryline device
----------------	--------------------------

FL SFP SX - Media module



2891754

<https://www.phoenixcontact.com/us/products/2891754>

Electrical properties

Current consumption	240 mA
Maximum power dissipation for nominal condition	0.8 W
Transmission medium	FO

Supply

Supply voltage	3.3 V (via Factoryline switch)
Power supply connection	via SFP slot
Max. current consumption	240 mA
Current consumption	240 mA

Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Case temperature	max. 85 °C (Operation)
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

Standards and regulations

Standard designation	Laser equipment safety
Standards/specifications	IEC 60825

FL SFP SX - Media module

2891754

<https://www.phoenixcontact.com/us/products/2891754>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2891754>



cUL Recognized
Approval ID: E140403



UL Recognized
Approval ID: E140403



DNV GL
Approval ID: TAA00000YV



LR
Approval ID: LR22250919TA



NK
Approval ID: TA24215M



BV
Approval ID: 48146_B0 BV



BSH
Approval ID: Nr. 966



RINA
Approval ID: ELE014724XG001



ABS
Approval ID: 21_2066186_1_PDA

FL SFP SX - Media module



2891754

<https://www.phoenixcontact.com/us/products/2891754>

Classifications

ECLASS

ECLASS-13.0	19179090
-------------	----------

ETIM

ETIM 9.0	EC000310
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL SFP SX - Media module

2891754

<https://www.phoenixcontact.com/us/products/2891754>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com