

## NLCV25T-R68M-PFR

## EOL Announced

Recommended Alternate Part No. : [NLCV25T-R68M-EFR](#) (Interchangeability is not guaranteed.)

## Product Status

Discontinue Issue Date : Nov.19, 2024

Last Purchase Order Date : Mar.31, 2026

Last Shipment Date : Sep.30, 2026

## Applications

Commercial Grade

## Feature

No Directivity

Wire Wound

Ferrite Core



## Series | Type

NLCV25-PFR

## Brand

TDK

## Environmental



RoHS



REACH



Halogen Free

## Compliance

Size	
Length(L)	2.50mm $\pm 0.20$ mm
Width(W)	2.00mm $\pm 0.10$ mm
Thickness   Height	1.80mm $\pm 0.10$ mm
Recommended Land Pattern (A)	1.00mm Nom.
Recommended Land Pattern (B)	1.50mm Nom.
Recommended Land Pattern (C)	1.50mm Nom.

## Electrical Characteristics

Inductance	680nH $\pm 20\%$ at 25.2MHz
Rated Current	1.26A
DC Resistance [Typ.]	90m $\Omega$
DC Resistance [Max.]	108m $\Omega$
Self Resonant Frequency [Min.]	160MHz
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	5 at 25.2MHz

## Other

Operating Temp. Range	-40 to 125°C (Including Self-Temp. Rise)
Soldering Method	Wave (Flow) Reflow Iron Soldering
AEC-Q200	NO

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.







## NLCV25T-R68M-PFR

Packing	Embossed (Plastic)Taping [180mm Reel]
Package Quantity	2000pcs
Weight	0.025g

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

## NLCV25T-R68M-PFR

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.



! All specifications are subject to change without notice.

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.