

[Skip to content](#)

[Corporate Home](#) | [Electronic Components](#) | [Segments](#) | [Who We Are](#)

Worldwide



Our commitment. Your advantage.

Search

By:



[Sign In](#) | [Register](#) ([Why Register?](#))

[Products](#)



- Connectors
- Electromechanical Components
- Electronic Modules
- Fiber Optics
- Filters
- Identification Labeling Products
- Passive Components
- Power Sources
- RF & Microwave Products
- Tooling Products
- Touch Screen Displays
- Tubing, Molded and Harnessing Products
- Wire, Cable and Cable Assemblies
- List all Product Types

Appliance

Automotive

Communications

Computer & Consumer

Electronics

Industrial & Commercial

Instrumentation & Medical

Equipment

By Brand

A to Z

Documentation

Find

Documents & Drawings

Find CAD Models

SPICE/Electrical Models

NAFTA Certificate of Origin

White Papers

Resources

RoHS

Compliance & Alternates

Cross Reference Products

Compare Multiple Products

Check Distributor Inventory

[Find Authorized Distributors](#)

[My Account](#)

[Sign In](#)

Register

Customer Support

Support

RoHS Support Center

Glossary of Terms

eBulletin Newsletter

[Home](#) > [Products](#) > [By Type](#) > [Modular Jacks & Plugs](#) > [Product Feature Selector](#) > Product Details

5-6605318-8 Product Details



5-6605318-8



[Active](#)

Integrated Magnetic, Stacked (Mag45™) and Power over Ethernet (PoE)



[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- 10/100BASE-T Ethernet Application
- Component Type = Single Port
- Magnetic Circuit = 326P13
- Turns Ratio = 1:1
- 1 x 1 Jack Configuration

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [1X1 MAG45\(TM\), 4N2P13 10/100 ETHERNET SCHEMATIC, 326...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Mag45* Modular Jacks With Integrated Magnetics](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)**Product Type Features:**

- Signal Routing Type = Auto MDI/MDIX, NIC
- [PCB Mount Style](#) = Thru Hole
- Shielded = Yes
- Shield Material = Brass

Mechanical Attachment:

- [Jack Configuration](#) = 1 x 1

Electrical Characteristics:

- [Component Type](#) = Single Port
- [Turns Ratio](#) = 1:1
- Impedance (Ω) = 100

Termination Related Features:

- [Bottom Panel Ground Tab](#) = Without

Body Related Features:

- [LED](#) = With
- Shield Panel Ground Tabs = With
- Latch Orientation = Standard - Latch Down
- [Bottom Shield](#) = Without
- Shield Plating = Semi-Bright Nickel (Pre-plated)
- PCB Tail Length (mm [in]) = 3.30 [0.130]

Housing Related Features:

- Housing Flammability Rating = UL 94V-0
- Housing Material = Thermoplastic Polyester (PET)

Configuration Related Features:

- Magnetic Circuit = 326P13
- Decoupling Capacitor = 2KV
- [Rear PCB Ground Tab](#) = Without
- Signal Lead Quantity = 8

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Left LED Color (Position #1) = Green
- Right LED Color (Position #2) = Yellow

Conditions for Usage:

- [Temperature Rating](#) = Office / Premises (0 °C to +70 °C)

Operation/Application:

- [Application](#) = 10/100BASE-T Ethernet

Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2007 Tyco Electronics Corporation All Rights Reserved