



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .151"
2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex								
8						DRAWN		G.R.S.	05/02/07										
7	HEAT SHRINK TUBING				1	CHECKED													
6	COVER	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	ISSUED				PART DESCRIPTION									
5	FERRULE	COPPER	GOLD	1		SHEET		1 OF 1		SMB R/A CRIMP PLUG (FOR RG-174/U, 316/U, 188/U DOUBLE BRAID)									
4	INSULATOR	PE	NATURAL	1						PART NO.									
3	CONTACT PIN	BER. COPPER	GOLD	1						142176									
2	INSULATOR	TEFLON	NATURAL	1															
1	BODY	BRASS	GOLD	1			CAD FILE		C:/142/142176.DWG		DWG. NO.		142176.DWG	REV.	B	SIZE	A	SCALE	NA
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING											