THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	20AUG17	F.P	I.Y
	A2	ECR-18-006317	25APR18	F.P	W.W
	A3	ECR-18-011273	18JUL18	B.Z	I.Y

CODINGS



CODE A | CODE B | CODE C | CODE D | CODE E | CODE F | CODE Z

1 HSD INTERFACE DESIGN ARE LEFT TO TE CONNECTIVITY

2 ALL DIMENSIONS IN BRACKETS ( ) FOR INFORMATION ONLY


3 PACKAGING: TAPE AND REEL


△4 MARKING OF 100% TEST PASSED

△5 AREA OF VACUUM GRIPPER


△6 CENTER OF GRAVITY


AS SHOWN 2315834-9, CODING Z







RECOMMENDED PCB LAYOUT










SCALE 2:1



QUANTITY							CODE	DESCRIPTION	MATERIAL	FINISH COLOR, SIMILAR RAL	ITEM NO.
						1		MQS PIN (LONG)	CuSn4	TIN PLATING	6
						1		MQS PIN (SHORT)			
						1		SHIELDING CAP	BRASS	TIN PLATING	5
						1		SHIELDING BODY	Zn ALLOY	SOLDER SIDE: TIN PLATING. INTERFACE SIDE(OUTER CONTACT): TIN PLATING.	4
						2		CONTACT PIN (LONG)	CuSn4	SOLDER SIDE: TIN PLATING. INTERFACE SIDE: GOLD PLATING	3
						2		CONTACT PIN (SHORT)			
						1		CAVITY BLOCK	PA4T-GF30	BLACK	2
							1	Z	PA6T/66	WATER BULE / 5021	1
						1		F		NUT BROWN / 8011	
					1			E		LEAF GREEN / 6002	
				1				D		CLARET VIOLET / 4004	
			1					C		SIGNAL BLUE / 5005	
		1						B		CREAM WHITE / 9001	
1								A		JET BLACK / 9005	

0-1	0-2	0-3	0-4	0-5	0-6	0-9
A	B	C	D	E	F	Z
1	1	1	1	1	1	1

ASSY NO. X-2315834-Y

ASSY CODE

REVISION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.5
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL - -

FINISH - -

DWN F.PAN 05JAN2017
CHK F.JIANG 0AUG2017
APVD I.YIN 0AUG2017

TE Connectivity

NAME HSD HEADER 90DEG 6POS. ASSY. -

PRODUCT SPEC 108-101388

APPLICATION SPEC -

WEIGHT -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	-	C-2315834	-

Customer Drawing | SCALE 5:1 | SHEET 1 OF 1 | REV A3

4805 (3/13)

Downloaded from Arrow.com.