



Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > SAS/SATA Solutions > Product Feature Selector > Product Details

1735183-1 Product Details

Share Print Email

1735183-1

TE Internal Number: 1735183-1

Active

View 3D PDF

Serial ATA & Serial Attached SCSI

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Without Shell
- Plug
- 29 Positions
- 1 Ports

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information	
Product Drawings: PLUG, SAS 15+7+7P 0.96MM OFFSET (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version B) 3D Model (IGES, Version B) 3D Model (STEP, Version B)	Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Product Type = Connector Connector Type = Plug PCB Mounting Orientation = Right Angle PCB Mount Style = Straddle Mount PCB Mount Retention = Without Mechanical Attachment: - Stackable = No Termination Features: Solder Tail Contact Plating = Tin over Nickel Body Features: Mount Type = PC Board (Direct Mount) Contact Features: Contact Base Material = Brass Contact Plating, Mating Area, Material = Gold (30) Housing Features: Housing Material = Liquid Crystal Polymer (LCP) Housing Color = Black UL Flammability Rating = UL 94V-0	Configuration Features: Shell = Without Number of Positions = 29 Number of Ports = 1 Plug Configuration = SAS Lightpipe = Without Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: High Temperature Housing = Yes Packaging Features: Packaging Method = Tray Packaging Quantity = 112 Other: Brand = TE Connectivity