

## Han 8 Quintax-M-c



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 008 3013
Specification	Han 8 Quintax-M-c
HARTING eCatalogue	<a href="https://b2b.harting.com/09150083013">https://b2b.harting.com/09150083013</a>

### Identification

Category	Inserts
Series	Han-Quintax <sup>®</sup> High Density
Description of the contact	for Han <sup>®</sup> D-Sub crimp contacts

### Version

Gender	Male
Number of contacts	8
further contacts	+ shielding
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm <sup>2</sup>
Rated current	5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance

## Material properties

Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	1
Net weight	27.4 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440218 Module for industrial connectors (data)