





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/4/09	
A		REVISED SHAPE	10/18/12	
B		UPDATE SPEC.	5/29/18	AY/SL
C		UPDATE DIM.	8/31/20	LH/EY



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon PA66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Current rating: 7 Amp

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 Ø.X ± .10
 .XX ± .020 Ø.XX ± .015
 .XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	1/4/09
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE .156 [3.96] HEADER, STRAIGHT		
SIZE X	PART NO. LHD-XX-TS-V0	REV. C
REF: S00019C	SCALE: NTS	SHEET 1 OF 1