AM2DR-LPZ

Click to ORDER samples



SIP7 Package

The AM2DR-LPZ is a 2W SIP7 DC/DC converter that offers great cost savings thanks to an improved manufacturing process. It also features excellent reliability and performance while offering a standard input voltage range of 5-24VDC as well as an output voltage of 3.3-24V. This compact SIP7 design will surely benefit your new system design.

This new series offers great operating temperatures, from -40 to 85°C with full power up to 71°C. Also, an isolation of 1500 or 3000VDC, improved reliability and system safety and a 3,500,000h MTBF comes standard.


The AM2DR-LPZ is suitable for instrumentation, industrial controls, industrial applications, communication and IoT applications.

Features

- High I/O Isolation of 1500/3000VDC
- Continuous Short circuit protection
- Operating Temp: -40 °C to +85 °C
- Industry standard SIP7 pin-out
- Efficiency up to 74%
- Regulated output

RoHS 3yr Warranty CE

Summary



Training

Product Training Video (click to open)

Press Release

Coming Soon!

Application Notes

Applications

IoT Industrial Telecom Portable Equipment

Downloaded from Arrow.com.

Models & Specifications

Single Output

Model	Input Voltage (VDC)	Output Voltage (VDC)	Input Current Full | No load typ. (mA)	Output Current max (mA)	Isolation (VDC)	Maximum capacitive Load (µF)	Efficiency Typ. (%)
AM2DR-0503SLPZ	5 (4.75-5.25)	3.3	556 / 6	400	1500	2400	67
AM2DR-0505SLPZ	5 (4.75-5.25)	5	556 / 6	400	1500	220	72
AM2DR-1203SLPZ	12 (11.4-12.6)	3.3	232 / 6	400	1500	2400	66
AM2DR-1205SLPZ	12 (11.4-12.6)	5	232 / 6	400	1500	220	72
AM2DR-1224SLPZ	12 (11.4-12.6)	24	232 / 6	83	1500	1000	74
AM2DR-1503SLPZ	15 (14.25-15.75)	3.3	186 / 6	400	1500	2400	67
AM2DR-1505SLPZ	15 (14.25-15.75)	5	186 / 6	400	1500	220	72
AM2DR-2403SLPZ	24 (22.8-25.2)	3.3	116 / 6	400	1500	2400	67
AM2DR-2405SLPZ	24 (22.8-25.2)	5	116 / 6	400	1500	220	72
AM2DR-0503SH30LPZ	5 (4.75-5.25)	3.3	556 / 6	400	3000	2400	67
AM2DR-0505SH30LPZ	5 (4.75-5.25)	5	556 / 6	400	3000	220	72
AM2DR-1203SH30LPZ	12 (11.4-12.6)	3.3	232 / 6	400	3000	2400	66
AM2DR-1205SH30LPZ	12 (11.4-12.6)	5	232 / 6	400	3000	220	72
AM2DR-1224SH30LPZ	12 (11.4-12.6)	24	232 / 6	83	3000	1000	74
AM2DR-1503SH30LPZ	15 (14.25-15.75)	3.3	186 / 6	400	3000	2400	67
AM2DR-1505SH30LPZ	15 (14.25-15.75)	5	186 / 6	400	3000	220	72
AM2DR-2403SH30LPZ	24 (22.8-25.2)	3.3	116 / 6	400	3000	2400	67
AM2DR-2405SH30LPZ	24 (22.8-25.2)	5	116 / 6	400	3000	220	72

Input Specification

Parameters	Conditions	Typical	Maximum	Units
Maximum rating	1 Sec(max), 5Vin models	> -0.7	9	VDC
	1 Sec(max), 12Vin models	> -0.7	18	VDC
	1 Sec (max), 15Vin models	> -0.7	21	VDC
	1 Sec (max), 24Vin models	> -0.7	30	VDC
Input reflected ripple current		15		mA
Filter	Capacitor			

Isolation Specification

Parameters	Conditions	Typical	Maximum	Units
Tested I/O voltage	60 sec, leakage ≤ 1mA	>1500		VDC
	60 sec, leakage ≤ 1mA for H30 models	>3000		VDC
Resistance	500VDC	>1000		MΩ
Capacitance	100kHz/0.1V	20		pF

Output Specification

Parameters	Conditions	Typical	Maximum	Units
Voltage accuracy			±3	%
Line regulation	Per 1% Vin change		±0.25	%
Load regulation**	10-100% load, 3.3Vout		±3	%

Downloaded from Arrow.com.

	10-100% load, others		±2	%
Ripple & Noise*		50	100	mV pk-pk
Temperature coefficient		±0.02		%/°C

* Ripple and Noise are measured at 20MHz bandwidth. Please refer to the application note for specific details.
** Operating with less than 10% of rated load will not cause permanent damage to the converters, but the performances data may not fall into the specifications, and reliable operating is not assured.

General Specifications


Parameters	Conditions	Typical	Maximum	Units
Switching frequency	Full load, nominal input	220		KHz
Short circuit protection	Continuous, Auto recovery			
Operating temperature	With derating at 71°C	-40 to +85		°C
Storage temperature		-55 to +125		°C
Case temperature rise	Ambient temperature at 25°C	25		°C
Manual soldering temperature	1.5mm away from case, duration ≤ 10sec		300	°C
Cooling	Free air convection			
Humidity	Non-condensing	>5	95	% RH
Vibration	10-150Hz, 5G, 0.75mm along all axis			
Case material	Black plastic (flammability to UL 94V-0)			
Weight		2.4		g
Dimensions (L x W x H)		0.77 x 0.28 x 0.40 inches (19.65 x 7.05 x 10.16 mm)		
MTBF	3 500 000 hrs (MIL-HDBK -217F, t=+25°C) / Full Load			

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.

Safety Specifications


Parameters		
Standards	Information technology Equipment	Designed to meet UL/EN/IEC 62368-1
	EMC - Conducted and radiated emission	CISPR32 / EN55032, class B with the recommended EMC circuit
	Electrostatic Discharge Immunity	IEC 61000-4-2 Air ±8KV, Contact ±6KV, Criteria B

Derating




Downloaded from Arrow.com.

Typical application circuit



Vin	Cin	Vout	Cout
5V	10μF, 16V	3.3V	10μF/16V
12V	4.7μF/25V	5V	4.7μF/16V
15V	2.2μF/25V	24V	1μF/50V
24V	1μF/50V		


Recommended EMC circuit




Models	C1/C2	CY
1500VDC	4.7μF/50V	1nF/2kVdc
3000VDC	4.7μF/50V	1nF/3kVdc

Downloaded from Arrow.com.

Dimensions





Grid size: 2.54*2.54mm

Note:
Unit: mm(inch)
General tolerance: ±0.50 (0.02)
Pin tolerance: ±0.1 (0.004)

Pin Out Specifications	
Pin	Single
1	+V Input
2	-V Input
4	-V Output
6	+V Output

NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. **2.** Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. **3.** Mechanical drawings and specifications are for reference only. **4.** All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. **5.** Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. **6.** This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. **7.** Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.

Downloaded from Arrow.com.