

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.



The marking on this product doesn't contain environmental hazardous materials per Material Specification 55-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

**FOR REFERENCE ONLY**



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
AX1	EDSR#6629	NON-RELEASE TO PRODUCTION	09/20/2016	Roger Tsai
AX2	EDSR#8410	CHG LCP TO NYLON6T	04/12/2018	Roger Tsai
AX3	EDSR#9260	ADDED PACKAGING	06/17/2019	Roger Tsai
AX4	EDSR#12004	UPDATED WHITE TO NATURAL, UPDATED PKG QUANTITY	03/15/2022	Roger Tsai


G800 LQ 268 XXX X DHR	1 x 40 = 40	101.60	99.06
G800 LQ 269 XXX X DHR	1 x 39 = 39	99.06	96.52
G800 LQ 270 XXX X DHR	1 x 38 = 38	96.52	93.98
G800 LQ 271 XXX X DHR	1 x 37 = 37	93.98	91.44
G800 LQ 272 XXX X DHR	1 x 36 = 36	91.44	88.90
G800 LQ 273 XXX X DHR	1 x 35 = 35	88.90	86.36
G800 LQ 274 XXX X DHR	1 x 34 = 34	86.36	83.82
G800 LQ 275 XXX X DHR	1 x 33 = 33	83.82	81.28
G800 LQ 276 XXX X DHR	1 x 32 = 32	81.28	78.74
G800 LQ 277 XXX X DHR	1 x 31 = 31	78.74	76.20
G800 LQ 278 XXX X DHR	1 x 30 = 30	76.20	73.66
G800 LQ 279 XXX X DHR	1 x 29 = 29	73.66	71.12
G800 LQ 280 XXX X DHR	1 x 28 = 28	71.12	68.58
G800 LQ 281 XXX X DHR	1 x 27 = 27	68.58	66.04
G800 LQ 282 XXX X DHR	1 x 26 = 26	66.04	63.50
G800 LQ 283 XXX X DHR	1 x 25 = 25	63.50	60.96
G800 LQ 284 XXX X DHR	1 x 24 = 24	60.96	58.42
G800 LQ 285 XXX X DHR	1 x 23 = 23	58.42	55.88
G800 LQ 286 XXX X DHR	1 x 22 = 22	55.88	53.34
G800 LQ 287 XXX X DHR	1 x 21 = 21	53.34	50.80
G800 LQ 288 XXX X DHR	1 x 20 = 20	50.80	48.26
G800 LQ 289 XXX X DHR	1 x 19 = 19	48.26	45.72
G800 LQ 290 XXX X DHR	1 x 18 = 18	45.72	43.18
G800 LQ 291 XXX X DHR	1 x 17 = 17	43.18	40.64
G800 LQ 292 XXX X DHR	1 x 16 = 16	40.64	38.10
G800 LQ 293 XXX X DHR	1 x 15 = 15	38.10	35.56
G800 LQ 294 XXX X DHR	1 x 14 = 14	35.56	33.02
G800 LQ 295 XXX X DHR	1 x 13 = 13	33.02	30.48
G800 LQ 296 XXX X DHR	1 x 12 = 12	30.48	27.94
G800 LQ 297 XXX X DHR	1 x 11 = 11	27.94	25.40
G800 LQ 298 XXX X DHR	1 x 10 = 10	25.40	22.86
G800 LQ 299 XXX X DHR	1 x 9 = 9	22.86	20.32
G800 LQ 300 XXX X DHR	1 x 8 = 8	20.32	17.78
G800 LQ 301 XXX X DHR	1 x 7 = 7	17.78	15.24
G800 LQ 302 XXX X DHR	1 x 6 = 6	15.24	12.70
G800 LQ 303 XXX X DHR	1 x 5 = 5	12.70	10.16
G800 LQ 304 XXX X DHR	1 x 4 = 4	10.16	7.62
G800 LQ 305 XXX X DHR	1 x 3 = 3	7.62	5.08
G800 LQ 306 XXX X DHR	1 x 2 = 2	5.08	2.54
<b>PART NUMBER</b>	<b>NO. OF POS.</b>	<b>A</b>	<b>B</b>



- NOTES:**
- INSULATOR: NYLON6T, UL 94V-0, COLOR- OPTION
  - CONTACT: COPPER ALLOY, "XXX"- PIN PLATING  
CONTACT/SOLDER AREA PLATING  
"005"- 15μ" GOLD/GOLD FLASH  
"010"- 30μ" GOLD/GOLD FLASH  
"018"- GOLD FLASH/GOLD FLASH  
"025"- 5μ" GOLD/GOLD FLASH  
"032"- 100μ" MATTE TIN/100μ" MATTE TIN  
UNDER 50μ" NICKEL PLATING OVERALL.
  - THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIALS PER DIRECTIVE 2011/65/EU FOR RoHS.
  - PACKING IS PER AMTA PACKING SPECIFICATION PKS-0001
  - PRODUCT SPECIFICATION REFER TO : PS-7501.

P/N: G800LQ XXX XXX X DHR

NO. OF POS. [ ] PLATING [ ] COLOR  
W: NATURAL  
Y: YELLOW



TOLERANCE	APPROVALS	DATE	TITLE		Amphenol®	
X. ±0.30	DRAWN Aqua Chou	03/15/2022	G800 SERIES, PCB HEADER 2.54 PITCH, SINGLE ROW, STR. PCB MOUNT, COLOR OPTION		Amphenol Corporation Amphenol Taiwan Corporation	
X.XX ±0.20	CHECKED Karen Su	03/15/2022				
X.XXX ±0.10	APPROVED Roger Tsai	03/15/2022			PART No.	G800LQXXXXXXDHR
ANGULAR ±1°	DWG TYPE CUST DWG	PROJECT CODE HEAD			UNIT mm	SIZE A3
UNLESS OTHERWISE SPECIFIED			SCALE NA	SHEET 1 OF 2	DWG No.	G800LQXXXXXXDHR


This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification 55-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

**FOR REFERENCE ONLY**



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
AX1	EDSR#6629	NON-RELEASE TO PRODUCTION	09/20/2016	Roger Tsai
AX2	EDSR#8410	CHG LCP TO NYLON6T	04/12/2018	Roger Tsai
AX3	EDSR#9260	ADDED PACKAGING	06/17/2019	Roger Tsai
AX4	EDSR#12004	UPDATED WHITE TO NATURAL, UPDATED PKG QUANTITY	03/15/2022	Roger Tsai



- NOTES:**
1. PE BAG SIZE : 195 X 265 mm
  2. INNER BOX SIZE : 215 X 175 X 150 mm
  3. SHIPPING CARTON SIZE : 370 X 230 X 175 mm

26~40	200	5	2,000
14~25	300	5	3,000
12~13	500	4	4,000
10~11	500	6	6,000
06~09	1000	6	12,000
05	2000	5	20,000
04	2000	5	20,000
03	2000	6	24,000
02	2000	15	60,000
POS.	PCS/ BAG	BAG/ INNER BOX	QUANTITY (PCS)

TOLERANCE	APPROVALS	DATE	TITLE		Amphenol®			
X. ±0.30	DRAWN Aqua Chou	03/15/2022	G800 SERIES, PCB HEADER 2.54 PITCH, SINGLE ROW, STR. PCB MOUNT, COLOR OPTION		Amphenol Corporation Amphenol Taiwan Corporation			
X.X ±0.20	CHECKED Karen Su	03/15/2022						
X.XX ±0.10	APPROVED Roger Tsai	03/15/2022						
ANGULAR ±1°	DWG TYPE CUST DWG	PROJECT CODE HEAD	UNIT mm	SIZE A3	PART No. G800LQXXXXXXXXDHR			
UNLESS OTHERWISE SPECIFIED			SCALE NA	SHEET 2 OF 2	DWG No. G800LQXXXXXXXXDHR REV. AX4			