Part Number : 192210227
Product Description : Compression Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 1/4" (M6), Plated, Wide Pad, Carton
Series Number : 19221
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : BCL-614-WP-PL



Documents and Resources

Drawings

192210227_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19901-017-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19221
Description	Compression Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 1/4" (M6), Plated, Wide Pad, Carton
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Battery Cable Lug
Style	Ring, Plated
Type	Battery Cable Lug
UPC	800753062269

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin

Downloaded from Arrow.com.

Net Weight	6.729/g
Packaging Type	Carton
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size (AWG)	6
Wire Size mm^2	10.50-16.80

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	192840034

Downloaded from Arrow.com.