


PXM6010/04S/CR/0709/SN Datasheet



Product Name // Flex Cable Connector PXM6010 Series 4

Contact Socket Crimp/Solder Termination (contacts available separately) 7mm-9mm Cable (Yellow Gland) Metal Body With Braid Termination

 [View Product Page](#)





// Product Description:

- Flex Cable Connectors
  - Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
  - 30 degree push twist locking, tamperproof lock prevents accidental un-mating
  - Socket
  - 4 Contacts
  - Crimp/solder termination with contacts and fitting tool available separately
- Metal Body With Braid Termination
  - Cable acceptance 7mm-9mm diameter
  - Gland Pack PXP6088 available separately to accomodate all sizes
  - PXM6081 Sealing Cap available separately to maintain IP rating of unmated connectors
  - Mate with PXM6011 Series Inline and PXM6012 Series Front Panel Mount Connectors

// General Information:

Product Display Title:	Flex Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Body Colour:	Metallic Grey
Body Material:	Brass
Body Material Type:	Metal Body With Braid Termination
Contact Type:	Socket Contact
Coupling Type:	Push-Twist
Current Max:	10A, 4A, 7A
Diameter Over Coupling Ring Mm:	32mm
Function:	Flex Cable Connector
Insulation Resistance:	>10 <sup>6</sup> MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	9mm
Min Cable Entry Size:	7mm
Max Contact Accomodation Awg:	20AWG
Min Contact Accomodation Awg:	16AWG
Max Contact Accomodation Mm2:	1.5mm2
Min Contact Accomodation Mm2:	0.5mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	4 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-11 Test Ka Salt Mist
Voltage Max:	277V

// Product PDF Links

-  6000 Series power connectors...
-  6000 Series metal body power...

// Product 3D CAD Model Links

-  PXM6010/04S/CR/0709/SN3D CAD Model



Have a question or project enquiry  
you'd like to talk to us about?



[Click Here To Contact Us](#)