Modulation Transformers *2000 Series*



Features:

- Sealed “gapped” core modulation transformer design
- Minimum frequency response of 150- 7000 Hz.
- Range of secondary taps for a variety of tube types
- The tapped secondary winding carries full class C plate current

RoHS

Parts

Part Number	Typical Modulation Push-Pull Tube Types	Watts	Primary Impedance (ohms)	Secondary Impedance (ohms)	Max. Secondary Current (DC)
2013	6V6, 6L6, 807, 5881, EL34	25	10000 C.T.	3000, 5000, 6500, 8000	100 mA

Tags: **modulation**, **transformers**, **gapped core**, **sealed core**, **class C plate current**

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.