

MICRO SWITCH



A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PREPONT, ILLINOIS

FED. MFR. CODE 91929

ASSEMBLY — PUSHBUTTON SWITCH

CATALOG LISTING

2PB281



NOTES

- 1 - UNIT INCLUDES "IISM TYPE" BASIC SWITCH (2) (D)
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- (4) MOUNTING HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ——— 30 OZ APPROX (C)	CONTACT ARRANGEMENT S P D T (2)	DO NOT SCALE PRINT
PRETRAVEL ——— .040 APPROX	250 VAC ——— 5 AMP	UNLESS OTHERWISE SPECIFIED
DIFFERENTIAL TRAVEL ——— .050 MAX	30 VOLTS DC RATING	DIMENSIONS ARE IN INCHES
(F) TOTAL TRAVEL ——— .110 APPROX	INDUCTIVE ——— SEA LEVEL ——— 3 AMP	TOLERANCES ARE:
	50,000 FT. ——— 2.5 AMP	ONE PLACE (.0) ± .030
	RESISTIVE ——— SEA LEVEL ——— 5 AMP	TWO PLACE (.00) ± .018
	50,000 FT. ——— 5 AMP	THREE PLACE (.000) ± .008
	MAXIMUM INRUSH ——— 24 AMP	ANGLES ±
		WEIGHT

2PB281

PAGE 1 OF 1

M

DRAWING
NUMBER

12

ISSUE

REPLACES

RELEASE NO. SR 8835

26 OCT 98

CHECK

26 FEB 60

CHECK

26 FEB 60

CHECK

26 FEB 60

CHECK

26 FEB 60

REVISIONS

A	CORR	M B F	4 MAR 60
B	COI4941	M B F	1 JULY 60
C	COI5142	L S D	28 SEP 60
D	COI7103	M B F	3 JAN 63
E	COI9900	H B W	18 JAN 65
F	CO21022	M B F	23 FEB 66
G	CO30742	R E R	2 OCT 72
H	CO31782	D B W	16 MAR 73
J	CO44047	R J W	7 APR 78
K	CO-93593	P P F	26 OCT 98
L	CO-94273	G J W	15 APR 99

ORMTEK
-30378
DRAWN