




Part Number : [1203410872](#)
Product Description : Micro-Change (M12)
CAT6A Double-Ended Cordset, 8 Poles, X-
Coded, Male (Straight) to Male (Straight), 26
AWG, Green Teal Shielded TPE Cable, 15.0m
(49.21') Length
Series Number : 120341
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : E22E06021M150



Documents & Resources

Drawings
[1203410872_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120341
Description	Micro-Change (M12) CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Male (Straight) to Male (Straight), 26 AWG, Green Teal Shielded TPE Cable, 15.0m (49.21') Length
IP Rating	IP67
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A,Industrial Ethernet
Protocol	EtherNet
Type	Double Ended
UPC	193264116270

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

Physical

Cable Diameter	7.30mm (.287")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Green Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Male-Male
Keyway	X-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass

Material - Plating Mating	Gold
Net Weight	130.500/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	Shielded TPE
Wire Size (AWG)	26

This document was generated on Mar 07, 2025
