



kingston.com/usb

IRONKEY D300S ENCRYPTED USB FLASH DRIVE

FIPS 140-2 Level 3 Certified

Kingston's IronKey™ D300S/SM USB Flash drive features an advanced level of security that builds on the features that made IronKey well respected, to safeguard sensitive information. It's FIPS 140-2 Level 3 certified, with 256-bit AES hardware-based encryption in XTS mode. An essential pillar to setting security standards, corporate policies and data loss protection (DLP) best practices. An important element in the quest for compliance with industry standards and global regulations such as the GDPR.

For added peace of mind, the drive uses digitally signed firmware, making it immune to BadUSB, and enforces complex password protection¹ with minimum characteristics to prevent unauthorised access.

Encryption and decryption is done on the drive, with no trace left on the host system, and the drive locks down and reformats after 10 invalid attempts to protect against brute force attacks.

Rugged and secure, IronKey D300S/SM has a zinc casing and tamper-evident epoxy seal for physical security, so you can rest assured the drive will hold up, even in the most demanding situations.

Customisable, easy to use and waterproof up to 4 feet, conforming to IEC60529 IPX83². SuperSpeed (USB 3.0) technology means you don't have to compromise on speed over security.

On top of its industry-leading data protection, IronKey D300S / D300SM provides a unique serial number and barcode printed on drive and virtual keyboard.³

Managed model

Requires SafeConsole or IronKey EMS software management system⁴. This allows central management of drive access and usage across thousands of drives.

Either cloud-based or on-premises, it enforces drive-specific policies, such as password strength and retry limits, and lets administrators remotely disable lost or stolen drives, recover lost passwords and more.

- › **Advanced level of security that builds on the features that made IronKey well-respected**
- › **Available in a Managed model that requires SafeConsole or IronKey EMS⁴**
- › **Rugged and secure casing that meets IronKey standards**
- › **Fast data transfers that use the latest in NAND Flash and controller technology**
- › **Customisable**
- › **Easy to use**
- › **NATO approved**

more >>

FEATURES / BENEFITS

Encrypted — With encryption, no one can access data that you have stored on the drive without knowing the password.

Meet frequently requested IT requirements — IronKey D300S/SM is FIPS 140-2 Level 3 certified and TAA compliant so you can rest assured it meets the most frequently requested corporate and government IT requirements.

Unique Serial Number and Scannable Barcode — To save time, simply read or scan the barcode when deploying, upon return or during any physical auditing.

Virtual Keyboard — Enables users to enter a password via mouse clicks, instead of using a physical keyboard; to reduce the risk of keylogging when using your encrypted drive on other computers.

SPECIFICATIONS

Interface

USB 3.1 Gen 1

Capacities⁸

4GB, 8GB, 16GB, 32GB, 64GB, 128GB

Speed⁹

USB 3.1 Gen 1

4GB: 80MB/s read, 12MB/s write

8GB & 16GB: 165MB/s read, 22MB/s write

32GB: 250MB/s read, 40MB/s write

64GB: 250MB/s read, 85MB/s write

128GB: 250MB/s read, 85MB/s write

USB 2.0

4GB: 30MB/s read, 12MB/s write

8GB-128GB: 30MB/s read, 20MB/s write

Dimensions

77.9 mm x 22.2 mm x 12.05 mm

Waterproof

Up to 4 ft.; conforms to IEC 60529 IPX8.

Product must be clean and dry before use.

Operating temperature

0°C to 60°C

Storage temperature

-20°C to 85°C

Compatibility

USB 3.0 compliant and 2.0 compatible

Minimum system requirements

– USB 3.0 compliant and 2.0 compatible

– two (2) free drive letters required for use

Compatible with

Windows® 10, Windows 8.1, Windows 8,

macOS (v. 10.14.x – 11.x.x)

Standard drive – compatible with

Windows® 10, Windows 8.1, Windows 8,

macOS (v. 10.14.x – 11.x.x), Linux v.2.6.x+⁷

Managed drive – compatible with

Windows® 10, Windows 8.1, Windows 8,

macOS (v. 10.14.x – 11.x.x)¹⁰



KINGSTON PART NUMBERS

| Serialised Standard | Serialised Managed |
|---------------------|--------------------|
| IKD300S/4GB | IKD300SM/4GB |
| IKD300S/8GB | IKD300SM/8GB |
| IKD300S/16GB | IKD300SM/16GB |
| IKD300S/32GB | IKD300SM/32GB |
| IKD300S/64GB | IKD300SM/64GB |
| IKD300S/128GB | IKD300SM/128GB |

COMPATIBILITY TABLE

| Operating System | D300S | D300S Managed | |
|-----------------------------|----------------|----------------|---------------------------|
| | | File Transfer | SafeConsole / IronKey EMS |
| Windows®10, 8.1, 8 | ✓ | ✓ | ✓ |
| macOS (v. 10.14.x – 11.x.x) | ✓ | ✓ | ✓ ¹⁰ |
| Linux v.2.6.x+ ⁷ | ✓ ₅ | ✓ ₆ | |

1. Password requirements set by administrator during set up using IronKey EMS for IronKey D300 Managed drives.
2. Product must be clean and dry before use.
3. Virtual Keyboard: Only supports US English on Microsoft Windows.
4. SafeConsole or [IronKey EMS Cloud Service End of Life \(EOL\) Announcement](#) by DataLocker, purchased separately.
5. D300S supports limited Linux commands, such as login, logout, initialise, about and forgot password.
6. D300SM supports limited Linux commands, such as login, logout and password change.
7. Certain distributions of Linux will require super-user (root) privileges in order to execute the IronKey commands properly in the terminal application window.
8. Some of the listed capacity on a Flash storage device is used for formatting and other functions and is thus not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide.
9. Speed may vary due to host hardware, software and usage.
10. D300SM macOS 11.x support expected Q2 2021.

