

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	ML10/13.SN
Product ID:	1SNA199105R2200
EAN:	3472591991055
Catalog Description:	ML10/13.SN Screw Clamp Terminal Blocks - Disconnect with lever - Black, Blue
Long Description:	- Simplify the disconnect operations for the disconnect terminal blocks installed next to fuse terminal blocks ML10/13.SF..., - With the same profile as ML10/13.SF, the ML10/13.SN disconnect lever is easily operated by hand and the wiring of the alternated disconnect and fuse circuits is easier, - Link bar for lever included in terminal block.

Ordering

Color:	Black, Blue
---------------	-------------

Minimum Order Quantity:	20 piece
--------------------------------	----------

Customs Tariff Number:	85361050
-------------------------------	----------

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
---	-----------------

Instructions and Manuals:	1SNC160019C0202
----------------------------------	-----------------

Dimensions

Product Net Width:	13 mm
---------------------------	-------

Product Net Height:	85 mm
----------------------------	-------

Product Net Depth / Length:	58 mm
------------------------------------	-------

Product Net Weight:	59 g
----------------------------	------

Technical

Rated Cross-Section:	10 mm ²
-----------------------------	--------------------

Spacing:	13 mm
-----------------	-------

Connection Type:	Screw clamp
-------------------------	-------------

Function:	Disconnect
------------------	------------

Number of Levels:	1
--------------------------	---

Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 10 mm ² Screw Clamp / Rigid 1x 0.5 ... 16 mm ²
--	---

Gauge Type:	A6
--------------------	----

Rated Current (I_n):	Main Circuit 16 A
---------------------------------------	-------------------

Rated Short-time Withstand Current (I_{cw}):	for 1 s 180 A
Rated Voltage (U_r):	800 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Pollution Degree:	3
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	12.0 mm
Recommended Screw Driver:	5.5 mm
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 10 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22 ... 10 AWG Stranded 10 AWG
Flammability According to UL94:	V0

Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161066A0201
cUL Certificate:	1SND161000A0203
Declaration of Conformity - CE:	1SND225015U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220021E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	172 mm
Package Level 1 Depth / Length:	155 mm
Package Level 1 Height:	71 mm
Package Level 1 Gross Weight:	1.18 kg
Package Level 1 EAN:	3472591991055
Package Level 2 Units:	200 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	300 mm
Package Level 2 Gross Weight:	12.300 kg
Package Level 3 Units:	4800 piece
Product Packing Type:	Box

