



1-1337434-0 Product Details

Share

Print

Email



Active

BNC RF Connectors

BNC RM BHJ Hex 50Ohm Silver Pltd RG58C/U

1-1337434-0

TE Internal Number: 1-1337434-0

Product Highlights

View All

- Connector - RF
- Jack
- Connector Style = Jack
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Connector - RF
Gender	Jack
Grade	Professional
Sealed	No
Isolated	No
Dielectric Material	PTFE
Flats Dimension	16.0 A/F

Mechanical Attachment

Surface Mountable	No
Hardware Included	No
Panel Mount Retention	With
Panel Mount Retention Type	Hex Nut
Panel Attachment Style	Rear Mount
Panel Cutout	12.0mm x 12.9mm D-Shape
Flange Dimension [A/F] (mm [in])	17.5 [0.689]
Hand Tool No.	9-1478240-0
Interchangeable Die Set Number	9-1478242-0

Electrical Characteristics

Connector Impedance (Ω)	50
Frequency	DC - 4 GHz

Termination Features

Coaxial Cable Termination Type	Crimp
Crimp Type	Hex
Crimp Dimensions	1.75 + 2.6 + 5.6 + 6.5

Dimensions

Panel Thickness (mm [in])	2.00 - 5.00 [0.078 - 0.197]
---------------------------	-----------------------------

Body Features

Body Style	Bulkhead
Body Material	Brass
Body Plating	Silver
Polarized	No
Ferrule Type	Hex
Flange and Thread Material	Brass
Lockwasher Material	Mild Steel
Lockwasher Plating	Silver
Gasket Material	White Silicone Rubber

Contact Features

Center Contact Material	Brass
Center Contact Plating	Silver

Housing Features

Connector Style	Jack
-----------------	------

Configuration Features

Coaxial Cable Type (RG/U or Mfg.)	141A, 58C, Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 71169Q, URM 43, URM 76
Number of Ports	1

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Converted to comply with RoHS directive
Military Style Number	UG-1804/U

Environmental

Operating Temperature (Max.) (°C)	165
-----------------------------------	-----

Conditions for Usage

Applies To	Coaxial Cable
------------	---------------

Packaging Features

Packaging Method	Individual
Packaging Quantity	50

Other

Brand	Greenpar
-------	----------

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

