




11TW401-1



TW Series Toggle Switch, 1 pole, 3 position, Solder terminal, Tab Lever

Actual product appearance may vary.

Features

Save space and weight
SPDT and DPDT circuitry
Temperature range: -85° F to +160° F (-65° C to +71° C)
Sealed bushing versions
Choice of 1/8 in. or 15/32 in. bushing
Color tab available on 15/32 in. bushing
UL recognized

Industrial machinery and equipment
Military and commercial aviation
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Description

MICRO SWITCH™ miniature toggle switches in two bushing sizes. Molded-in terminals are plated for soldering. Momentary and maintained circuitry closures available. Special on-on-on circuitries are also available. Pull-to-unlock levers prevent accidental operation.

Supporting Documentation

[Accessory: Lever Sleeve](#)

[Accessory: Seals](#)

[Accessory: Nuts](#)

[Engineering Drawing](#)

Product Specifications			
Circuitry/Operating action	Keyway Position	Center Position	Opposite Keyway Position
Product Type	MICRO SWITCH™ Toggle Switch		
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac, 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc		
Circuitry	SPDT		
Action	3 position		
Mounting	Bushing 15/32 in		
Termination	Solder		
Lever Type	Tab		
UL/CSA Rating Code	L117: 5 A at 125 Vac		
Comment	Fine silver contacts		
Availability	Global		
UNSPSC Code	30211908		
UNSPSC Commodity	30211908 Toggle switches		
Series Name	TW		

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback