THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2000
© COPYRIGHT 2000 - ALL RIGHTS RESERVED.

REVISIONS					
LOC	DIST	P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		C	REVISED PER ECO-12-006972	21AUG2012	KH	JE

△2 PHOSPHOR BRONZE

△3 LCP, UL94V-0

△4 FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT TIN-LEAD OVER BASE PLATING.

△5 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.


△6 REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.

△7 APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD.


△8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.


△9 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.


△10 HOLE DIAMETER SHOULD BE 3.10 WHEN USING FEED THROUGH GUIDE PIN P/N 120759.
CLEARANCE FOR M3x0.5 THREAD.




SECTION B-B








RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD





SIGNAL CONTACT LOCATION REF

ROWS A,B,C,D,E ROW F: 2-5	ROW F:1	120993-1
SIGNAL CONTACT TYPE B QTY: 29 9.7 LENGTH REF	SIGNAL CONTACT TYPE A QTY: 1 8.2 LENGTH REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±0.05
4 PLC ±-
ANGLES ±-

MATERIAL HOUSING: △3 CONTACTS: △2
FINISH -
SIGNAL CONTACT: △4

DWN B.CARBO 26JUL2006
CHK R.PATTERSON 26JUL2006
APVD R.PATTERSON 26JUL2006

TE Connectivity

NAME HEADER ASSEMBLY, 30 POSITION, SEQUENCED, RIGHT HAND, 6 ROW, Z-PACK HS3

PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-120993	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV C

4805 (3/11)

Downloaded from Arrow.com.