

80mm sq.**San Ace 80**


15mm thick, 20mm thick, 25mm thick
 25mm thick (San Cooler), 32mm thick
 38mm thick (GV type), 38mm thick (G type)

**General Specifications** With a pulse sensor

- Material.....Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1)
- Life ExpectancyVaries for each model (L10: Survival rate: 90% at 60°C,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black (Sensor) yellow
- Storage Temperature ...-30°C to +70°C (Non-condensing)

80×80×38mm [Mass : 220g]**GV type****Specifications**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Air Flow		Static Pressure		SPL	Operating Temperature	Life Expectancy
						[m ³ /min]	[CFM]	[Pa]	[inchH ₂ O]	[dB(A)]	[°C]	[h]
9GV0812G101	12	10.8 to 13.2	3.80	45.60	10,200	3.90	138.0	490.0	1.97	65	-10 to +70	40,000

Dimensions (Unit : mm)**Reference dimension of mounting holes and vent opening (Unit : mm)**