

Honeywell Sensing and Control




Home> Products > Standard Precision Switches > SX > Product Page

▼ Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Customer Feedback

1SX74-T



Actual product appearance may vary.

SX Series Subminiature Basic Switch, Single Pole Double Throw (SPDT), 250 Vac, 7 A, Pin Plunger Actuator, Solder Termination

Features

Long operating life
Elongated mounting hole for easier, more accurate mounting
Choice of actuation (plunger, as well as a variety of integral and auxiliary actuators)
Choice of electrical termination (solder, quick connect, PCB)
Choice of operating characteristics
Optional series constructions available (gold contacts for low energy switching, bifurcated gold contacts for maximum reliability, power load switching capability to 7 A)
MIL-PFR-8805 qualified listings available

Potential Applications

Aerospace
Appliances
Vending machines
Timing devices
Office equipment
Computer/business equipment
Test instruments
Medical/dental equipment
Communications equipment
HVAC equipment
Manually operated devices
Valves

Description

SX Series Subminiature Basic Switches are used for simple or precision on/off application needs. They are small, precision snap-action switches that are ideal where savings in space and weight are important.

Supporting Documentation

📄 [Engineering Drawing](#)

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.



Product Search

Part number search:



Use (*) to expand search

→ [Specification Search](#)

Product Specifications

Switch Type	Subminiature 10,2 mm H x 5,08 mm W x 12,7 mm L [0.4 in H x 0.20 in W x 0.5 in L]
Sealed	No
Ampere Rating	7 A
Circuitry	Single Pole Double Throw (SPDT)
Actuator	Pin Plunger
Termination	Solder
Operating Temperature Range	-53 °C to 121 °C [-65 °F to 250 °F]
Voltage	250 Vac
Approvals	CSA,UL
Contact Type	Silver
Operating Force (O.F.)	1,39 N [5.0 oz] max.
Release Force (R.F.)	0,28 N [1.0 oz] min.
Pretravel (P.T.)	0,5 mm [0.020 in] max.
Overtravel (O.T.)	0,25 mm [0.010 in] min.
Differential Travel (D.T.)	0,13 mm [0.005 in] max.

Operating Position (O.P.)	8,13 mm \pm 0,38 mm [0.320 in \pm 0.015 in]
Housing Material	General Purpose Phenolic
High Temperature	121 °C [250 °F]
CE mark	61058-1
UL File #	E12252
CSA File #	LR41372
Agency Approvals and Standards	1054
Mounting Screw Size	22,1 mm [0.087 in]
Mounting Centers	4,83 mm [0.19 in]
Maximum Tightening Torque	0,22 N m [2.0 in lb]
Weight	1,36 g [0.003 lb]
Package Height	8,89 mm [0.35 in]
Package Width	5,0 mm [0.20 in]
Package Length	12,7 mm [0.50 in]
Recommended For	Most applications
Comment	Turret type solder terminals.
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	SX

[Terms & Conditions](#) |
 [Privacy Statement](#) |
 [Site Map](#)