

Wall-Mount Fiber Optic Distribution Enclosure, 4-Panel Capacity

MODEL NUMBER: **N492-WM4-BK**



Convenient, secure and fully sealed wall-mount fiber optic enclosure for managing and protecting your fiber terminations. Compatible with Tripp Lite high-density fiber adapter panels.

Description

The N492-WM4-BK Wall-Mount Fiber Optic Distribution Enclosure manages and protects your fiber terminations where space is at a premium. It locks using the included key to keep your connections safe from tampering. The doors open wide to reveal plenty of room for splicing and patching your fiber cabling. It supports up to four fiber adapter panels, such as Tripp Lite's high-density LC (N492-08D-LC), SC (N492-06D-SC) and ST (N492-08S-ST) panels. Cable manager rings, cable ties and a labeling sticker help you keep your cables neatly organized inside the fully sealed enclosure. Made from heavy-duty cold-rolled steel, the N492-WM4-BK mounts on any solid surface.

Features

Fully Sealed Enclosure Manages and Protects Your Fiber Terminations

- Patch and splice cabling in a single enclosure
- Mounts securely on any solid surface
- Locks with included key to protect connections against tampering
- Heavy-duty cold-rolled steel construction
- Cable manager rings, cable ties and label included for organized cable management
- Supports up to 4 Tripp Lite fiber adapter panels, including N492-08D-LC, N492-06D-SC and N492-08S-ST

Specifications

OVERVIEW	
UPC Code	037332202925
Technology	Multimode; Singlemode

Highlights

- Mounts securely on any solid surface
- Locks with included key to protect connections against tampering
- Made from heavy-duty cold-rolled steel
- Includes rings, ties and label for organized cable management
- Supports up to 4 Tripp Lite fiber adapter panels

Package Includes

- N492-WM4-BK Wall-Mount Fiber Optic Distribution Enclosure, 4-Panel Capacity
- (4) Cable manager rings
- (5) Cable ties
- Cable lock post
- Label
- (2) Keys
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	17.02 x 47.50 x 36.83
Shipping Dimensions (hwd / in.)	6.70 x 18.70 x 14.50
Shipping Weight (kg)	5.81
Shipping Weight (lbs.)	12.80
Unit Dimensions (hwd / in.)	11.4 x 14.3 x 4.2
Unit Dimensions (hwd / cm)	29 x 36.3 x 10.7
ENVIRONMENTAL	
Operating Temperature	-40 to 60 C (-40 to 140 F)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>