



**Part Number :** [1300550003](#)

**Product Description :** Brad RJ-Lnxx Industrial Ethernet Receptacle, Female (Straight) to Male (Straight), 10Base T, Solder PCB and Cable Termination, 0.305m (1.0') Length

**Series Number :** 130055

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** ENSP1F5C305-V

---

## Documents and Resources

### Drawings

[1300550003\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## CE - Declaration of Conformity

## UKCA - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130055
Description	Brad RJ-Lnxx Industrial Ethernet Receptacle, Female (Straight) to Male (Straight), 10Base T, Solder PCB and Cable Termination, 0.305m (1.0') Length
IP Rating	IP67
Product Name	Brad,RJ-Lnxx
Type	Adapter
UPC	78678850480

### Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V DC

### Physical

Coupling Type	External Thread
Gender	Male
Keyway	None
Length	0.305m
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Net Weight	4.980/g
Orientation	Straight
Panel Mount	Front

Poles	N/A
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

---

This document was generated on May 23, 2026