


SPECIFICATION CONTROL DRAWING



APPLICATION

- This adapter is available in two platings:
 Y = B: Olive Drab Cadmium in accordance with QQ-P-416 over a suitable underplate to withstand 500 hr. salt spray test.
 Y = C: Electroless Nickel in accordance with MIL-C-26074 to withstand 48 hr. salt spray test.
- This adapter is designed to be mounted on connectors from ROCKWELL-COLLINS AVIONICS.
- Used in conjunction with 9 ferrules HET-A-02Y or HET-A-03Y.

INSTALLATION

- See Raychem installation procedure RPIP-696-00 except paragraph (1) dimension B to be determined according to application.
- Recommended coupling torque: 11 mN (95 Lbf. in.)

PACKAGING

- All components will be supplied in a plastic bag, inside a box.

KIT DESCRIPTION

6	2	Retention Clips	Aluminum Alloy	HEXDB-R-AY-21
5	4	Screw 4-40 UNC 2A	Stainless Steel	
4	1	Box	Aluminum Alloy	HEXDB-B-AY-21-03
3	1	Holding Nut	Aluminum Alloy	HEXDB-E-AY-21
2	4	Adaptor	Aluminum Alloy	HEXDB-C-AY21
1	1	HEX40-AY-90-21-A9-1	Aluminum Alloy	HEX40-AY-90-21-A9-1
Item	Qty.	Description	Material	Individual Product Name

*A trademark of Raychem Corporation.

Raychem		THERMOFIT DEVICES		Raychem Corporation 300 Constitution Drive Menlo Park, CA 94025 USA		TITLE: Right Angle HexaShield Dog Box Kit for Rockwell Collins Equipment	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS.				DOCUMENT NO. HEXDB-AY-90-A9-1			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A		ANGLES: N/A		Raychem reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		DCR NUMBER: D981869	
ROUGHNESS IN MICRON						REPLACES: D980709	
DRAWN BY: M. FORONDA		DATE: 15-Oct-98		REV. D		DOC ISSUE: 3	
				SCALE: None		SIZE: A	
						SHEET: 1 of 1	

If this document is printed it becomes uncontrolled. Check for the latest revision.