



DSG

KC-99-40



MOUNTING HOLE

DSG

- NOTES:**
1. INTERFACES PER MIL-STD-348, FIG. 301-2.
 2. MATERIALS:
INSULATORS-TEFLON, ASTM-D-4894
CENTER CONTACT-BER. COP., ASTM-B-196
ALL OTHER METAL PARTS-BRASS, ASTM-B16
 3. FINISHES:
ALL METAL PARTS-SILVER PLATE PER QQ-S-365
 4. ELECTRICAL CHARACTERISTICS:
NOMINAL IMPEDANCE-50 OHMS
WORKING VOLTAGE-500 VRMS
FREQUENCY RANGE-DC TO 4 GHz

- UNLESS OTHERWISE SPECIFIED
1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
 - 3 PLACE DECIMALS $\pm .004$ ANGLES $\pm 1^\circ$
 - CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.
 2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
 3. NO FILLETS PERMITTED.
 4. SURFACE ROUGHNESS 63 MICRONS/INCHES RMS MAX.
 5. ALL DIMENSIONS PRIOR TO PLATING.
 6. ALL PLATING IN ACCORDANCE WITH RCR 10004.
 7. ALL LEAD THREADS TO BE CHAMFERED 45° TO ROOT DIAMETER.
#CRITICAL DIMENSIONS

ADAPTER, F-F, BULKHEAD ISOLATED GROUND, BNC-BNC	DRAWN	KH	09/06/95
	DESIGN	CT	09/07/95
	APPR.		DATE

WALKERS
ELECTRONICS CO., INC.
ROCK HILL, SOUTH CAROLINA 29730

KC-99-40