













Available Headstyles

Headstyles	Diameter • Plating	
A 	1,50 • Au/Rh/Ni	
B 	1,00 • Au/Rh/Ni	
BST 	0,62 • Au/Ni	
C 	1,50 • Au	2,00 • Au
C1 	2,3/3,2 • Au	
C2S 	2,40 • Au (HTK)	
D 	1,00 • Au	1,50 • Au/Ni
D1 	0,64 • Au	
E 	1,50 • Au/Ni	
G 	1,30 • Au/Rh/Ni	1,50 • Au/Ni
H 	1,50 • Au/Rh/Ni	
K/KL4 	1,50 • Au	
M 	1,50 • Au	
M1 	1,40 • Au/Ni	
Q/QL4 	1,30 • Au/Rh/Ni (nur Q)	
	1,50 • Au/Ni	

Q5 	1,00 • Au/Ni	
V/VL4 	1,00 • Au/Ni	

Series 1025 • 1025/Z

Mechanical

Spacing	2,54 mm/100 mil
Full travel	6,30 mm
Recommended working travel	5,00 mm
Pre-loaded spring force	0,50/0,50/0,50/0,50 N only BST: 0,40/0,40/0,40 N
Spring force at working travel (± 20%)	1,10/1,50/2,25/3,00 N only BST: 1,50/2,25/3,00 N

Electrical

max. current rating	3,0 A
Typ. continuity resistance	≤ 25 mOhm

Materials

Barrel	bronze, gold plated
Spring	spring steel, gold plated
Plunger	steel
Receptacle	bronze, gold plated

Recommended Diameter of Drill


HP 2361.1 (Trolitax)	1,65 mm
with inserted press ring	1,75 mm
HGW 2372	1,67 mm
with inserted press ring	1,76mm

How to order:

1025 - D - 1,5 N - Au - 1,5

Series Headstyle Contact Pressure Plating Tip Diameter (mm)

Dimensions and Mounting Measures



*short version for easy-pull-off of broken pins.

Also available:
H 1025 L-K
H 1025 W-K