


CGA2B2X7R1E223K050BA

| | |
|---------------------------------|---|
| Product Status | Production |
| TDK Item Description | CGA2B2X7R1E223KT**** |
| Applications | Automotive Grade |
| Feature | AEC-Q200 AEC-Q200 GeneralGeneral (Up to 50V) |
| Series | CGA2(1005) [EIA 0402] |
| Brand | TDK |
| Environmental Compliance | |









| Size | |
|-------------------------------|------------------|
| Length(L) | 1.00mm ±0.05mm |
| Width(W) | 0.50mm ±0.05mm |
| Thickness(T) | 0.50mm ±0.05mm |
| Terminal Width(B) | 0.10mm Min. |
| Terminal Spacing(G) | 0.30mm Min. |
| Recommended Land Pattern (PA) | 0.30mm to 0.50mm |
| Recommended Land Pattern (PB) | 0.35mm to 0.45mm |
| Recommended Land Pattern (PC) | 0.40mm to 0.60mm |

| Electrical Characteristics | |
|------------------------------|-----------|
| Capacitance | 22nF ±10% |
| Rated Voltage | 25VDC |
| Temperature Characteristic | X7R(±15%) |
| Dissipation Factor (Max.) | 3% |
| Insulation Resistance (Min.) | 10000MΩ |

| Other | |
|-----------------------|------------------------------------|
| Operating Temp. Range | -55 to 125°C |
| Soldering Method | Reflow |
| AEC-Q200 | YES |
| Packing | Punched (Paper)Taping [180mm Reel] |
| Package Quantity | 10000pcs |

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Associated Images

