



Pushing Performance  
Since 1945

# M12 POWER PFT FEMALE L-CODED REAR 1,5mm



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 596 2515
Specification	M12 POWER PFT FEMALE L-CODED REAR 1,5mm
HARTING eCatalogue	<a href="https://b2b.harting.com/21035962515">https://b2b.harting.com/21035962515</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	Panel feed through
Specification	With conductors for rear mounting

## Version

Gender	Female
Shielding	Unshielded
Number of contacts	5
Number of power contacts	4
Number of special contacts	1
Specification of special contacts	FE contact
Coding	L-coding
Locking type	Screw locking

## Technical characteristics

Conductor cross-section	1.5 mm <sup>2</sup>
Conductor cross-section	AWG 16
Rated current	16 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV



**Pushing Performance**  
Since 1945

## Technical characteristics

Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	2 Nm Lock nut
Wrench size	17 18
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 100$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I ( $600 \leq \text{CTI}$ )
Conductor length	30 cm

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-111
----------------	-----------------



Pushing Performance  
Since 1945

Specifications and approvals

UL / CSA	UL 2238 CYJV2.E302521
	CSA-C22.2 No. 182.3 CYJV8.E302521

Commercial data

Packaging size	1
Net weight	49.75 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140227712
eCl@ss	27440103 Sensor-actuator connector chassis (sensor technology acc.)