


# SPACER

## Hexagonal Threaded Spacer (M3) [SP, SQ Series] (100pcs/pack)

<b>Material</b>	Brass
<b>Finish</b>	Ni plating

Model No.	A (mm)	L (mm)	Model No.	A (mm)	L (mm)	Model No.	A (mm)	L (mm)
SP-3	Through	3	SP-16	Through	16	SP-30	10	30
SP-4	Through	4	SP-17	Through	17	SP-35	10	35
SP-5	Through	5	SP-17.5	Through	17.5	SP-40	10	40
SP-6	Through	6	SP-18	Through	18	SP-45	10	45
SP-7	Through	7	SP-19	Through	19	SP-50	10	50
SP-7.5	Through	7.5	SP-20	Through	20	SP-55	10	55
SP-8	Through	8	SP-21	10	21	SP-60	10	60
SP-9	Through	9	SP-22	10	22	SP-65	10	65
SP-10	Through	10	SP-23	10	23	SP-70	10	70
SP-11	Through	11	SP-24	10	24	SP-75	10	75
SP-12	Through	12	SP-25	10	25	SP-80	10	80
SP-12.5	Through	12.5	SP-26	10	26	SP-85	10	85
SP-13	Through	13	SP-27	10	27	SP-90	10	90
SP-14	Through	14	SP-28	10	28	SP-95	10	95
SP-15	Through	15	SP-29	10	29	SP-100	10	100



Model No.	A (mm)	L (mm)	Model No.	A (mm)	L (mm)	Model No.	A (mm)	L (mm)
SQ-4	2 more	4	SQ-17	10	17	SQ-35	10	35
SQ-5	2	5	SQ-17.5	10	17.5	SQ-40	10	40
SQ-6	3	6	SQ-18	10	18	SQ-45	10	45
SQ-7	4	7	SQ-19	10	19	SQ-50	10	50
SQ-7.5	4	7.5	SQ-20	10	20	SQ-55	10	55
SQ-8	4	8	SQ-21	10	21	SQ-60	10	60
SQ-9	4	9	SQ-22	10	22	SQ-65	10	65
SQ-10	6	10	SQ-23	10	23	SQ-70	10	70
SQ-11	6	11	SQ-24	10	24	SQ-75	10	75
SQ-12	6	12	SQ-25	10	25	SQ-80	10	80
SQ-12.5	6	12.5	SQ-26	10	26	SQ-85	10	85
SQ-13	6	13	SQ-27	10	27	SQ-90	10	90
SQ-14	6	14	SQ-28	10	28	SQ-95	10	95
SQ-15	10	15	SQ-29	10	29	SQ-100	10	100
SQ-16	10	16	SQ-30	10	30			

