

External 240V Rackmount Battery Pack for select Tripp Lite UPS Systems (BP240V5RT2U)

MODEL NUMBER: **BP240V5RT2U**



Highlights

- BP240V5RT2U is a replacement external battery pack intended to replace the original battery pack bundled with Tripp Lite SmartOnline SU5000RT3UHV UPS Systems
- 240VDC battery pack with convenient DC input connector

Description

Tripp Lite's BP240V5RT2U is a 2U external battery pack that serves as a replacement for the original battery pack bundled with Tripp Lite SmartOnline SU5000RT3UHV UPS Systems. Includes a simple DC input connection for fast installation.

NOTE - A maximum of ONE BP240V5RT2U can be connected to each SU5000RT3UHV installation (see specification table).

Features

- 2U external battery pack that serves as a replacement for the original battery pack bundled with Tripp Lite SmartOnline SU5000RT3UHV UPS Systems
- Includes a simple DC input connection for fast installation

Specifications

OVERVIEW	
UPC Code	037332122537
INPUT	
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9
Input Connection Type	Modular 3-wire DC connector
Input Phase	Single-Phase
BATTERY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Expandable Battery Runtime	This battery pack has no DC jack to connect more battery packs - and can only be used in a multiple battery installation as the final battery pack in the chain of connected battery packs. For additional battery packs beyond the single BP240V5RT2U provided with your SU5000RT3UHV UPS, use BP240V10RT3U which does include a DC jack to support the connection of multiple battery packs.
DC System Voltage (VDC)	240
UPS Connection	Black 3-point DC connector
PHYSICAL	
Material of Construction	Steel
External Battery Pack Form Factor	Rack
Installation Form Factor Notes	Upright vertical tower configuration is not recommended for this model
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	Wallmount (2POSTRMKITWM)
Minimum Required Rack Depth (cm)	73.02
Minimum Required Rack Depth (inches)	28.75
Rack Height	2U
Shipping Dimensions (hwd / cm)	24.13 x 67.31 x 72.39
Shipping Dimensions (hwd / in.)	9.50 x 26.50 x 28.50
Shipping Weight (kg)	59.87
Shipping Weight (lbs.)	132.00
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 20.75
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 52.7
Unit Weight (lbs.)	90.4
Unit Weight (kg)	41.00
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>