



# DE11XRA330KJ4BQ01F



## Appearance & Shape



## References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B         | Bulk(Bag)      | 500                       |

| Mass (typ.) |      |
|-------------|------|
| 1 piece     | 0.2g |

## Notices

X1/Y1 Class Certified Products、 Halogen-free Products、 Rated Voltage X1:500Vac(r.m.s.)/Y1:500Vac(r.m.s.)/1.5kVdc

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# DE11XRA330KJ4BQ01F



## Specifications

|                                                  |                        |
|--------------------------------------------------|------------------------|
| L size or Outer diameter D                       | 7.0mm max.             |
| T size                                           | 5.0mm max.             |
| Lead spacing F                                   | 10.0±0.8mm             |
| Lead diameter d                                  | 0.6±0.05mm             |
| Paint dripping e                                 | Up to the end of crimp |
| Capacitance                                      | 33pF ±10%              |
| Rated voltage                                    | 500Vac(r.m.s.)         |
| Temperature characteristics                      | SL(JIS)                |
| Temperature range of temperature characteristics | 20°C to 85°C           |
| Operating Temperature Range                      | -40°C to 125°C         |
| TC                                               | +350 to -1000ppm/°C    |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# DE11XRA330KJ4BQ01F




## Characteristic Data


The charts below may show another part number which shares its characteristics.




DE11XRA330KJ4BQ01F |Z| DCOV, 20degC



DE11XRA330KJ4BQ01F R DCOV, 20degC



DE11XRA330KJ4BQ01F C-DC bias capchange, 20.0




DE11XRA330KJ4BQ01F C-AC Voltage capchange, 1


### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# DE11XRA330KJ4BQ01F



DE11XRA330KJ4BQ01F C-Temp. capchange, DCOV,



DE11XRA330KJ4BQ01F S21 DCOV, 20degC

## Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.