

Uninterruptible power supply - TRIO- UPS-2G/1AC/1AC/120V/750VA - 2905908

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



1AC/1AC/750 VA uninterruptible power supply with integrated power storage, lead AGM, VRLA technology, 24 V DC, 3.4 Ah for 120 V AC applications.

Product Description

UPS modules with integrated energy storage are particularly space saving: UPS module and energy storage are combined in one housing. It's just a case of connecting a power supply upstream.


The TRIO AC-UPS ensures seamless transition to battery operation thanks to the pure sine curve. Connected industrial PCs can be shut down safely via the integrated USB interface.

Why buy this product

- ✓ Smooth transition, thanks to the pure sine curve: the sine generated in battery operation is synchronous with the mains previously used for supply
- ✓ Space saving: UPS module and energy storage combined in one housing
- ✓ Long buffer times with integrated VRLA energy storage, can be extended with additional energy storage
- ✓ USB interface for connection to higher-level controllers such as industrial PCs
- ✓ Startup from energy storage possible, even without mains input



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 007397
GTIN	4055626007397
Weight per Piece (excluding packing)	6,120.000 g
Custom tariff number	85371091
Country of origin	Germany

Technical data

Dimensions

Uninterruptible power supply - TRIO-UPS-2G/1AC/1AC/120V/750VA - 2905908

Technical data

Dimensions

Width	210 mm
Height	170 mm
Depth	136 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	-15 °C ... 40 °C (with charged power storage device)
Max. permissible relative humidity (operation)	≤ 95 % (25°C, non-condensing)
Noise immunity	EN 61000-6-2

Input data

Nominal input voltage	120 V AC
Input voltage range	96 V AC ... 138 V AC
AC frequency range	55 Hz ... 65 Hz
Input fuse	10 A 400 V gRL
Permissible backup fuse	B10 B16 Listed breaker
Power factor (cos phi)	0.8

Output data

Nominal output voltage	120 V AC
Nominal output current (I _N)	6 A
Connection in parallel	No
Connection in series	No

General

Net weight	5.7 kg
Memory medium	Lead rechargeable battery module
Protection class	I
MTBF (IEC 61709, SN 29500)	> 206000 h (40°C)

Connection data, input

Connection method	Push-in connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12

Uninterruptible power supply - TRIO-UPS-2G/1AC/1AC/120V/750VA - 2905908

Technical data

Connection data, output

Connection method	Push-in connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12

Signaling

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	1.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	16

Charging process

Charging time	7 h
---------------	-----


Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2
Standards/regulations	EN 61000-4-2
Contact discharge	4 kV (Test Level 2)
Standards/regulations	EN 61000-4-3
Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m
Standards/regulations	EN 61000-4-4
Comments	Criterion B
Standards/regulations	EN 61000-4-5
Signal	1 kV (Test Level 2 - asymmetrical)
Standards/regulations	EN 61000-4-6
Frequency range	0.15 MHz ... 80 MHz
Voltage	10 V
Standards/regulations	EN 61000-4-8
UL approvals	UL/C-UL Recognized UL 1778
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC

Uninterruptible power supply - TRIO-
UPS-2G/1AC/1AC/120V/750VA - 2905908

Drawings

Block diagram



Approvals




Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 342453
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 342453
cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	

