

Ød ±0.05	p = 10	p > 10	p = 37.5
	0.6	0.8	1.0

All dimensions are in mm.

PRODUCT CODE SYSTEM

The part number, comprising 14 digits, is formed as follows:



- Digit 1 to 3 Series code.
- Digit 4 d.c. rated voltage:
C =50V D =63V E =100V G =160V
I =250V M=400V P =630V Q =1000V
- Digit 5 Pitch:
F=10mm; I=15mm; N=22.5mm; R=27.5mm;
W=37.5mm
- Digit 6 to 9 Digits 7 - 8 - 9 indicate the first three digits of Capacitance value and the 6th digit indicates the number of zeros that must be added to obtain the Rated Capacitance in pF.
- Digit 10 to 11 Mechanical version and/or packaging (table 1)
- Digit 12 Identifies the dimensions and electrical characteristics.
- Digit 13 Internal use
- Digit 14 Capacitance tolerance:
J=5%; K=10%; M=20%.

Table 1 (for more detailed information, please refer to page 14)

Standard packaging style	Lead length (mm)	Taping style			Ordering code (Digit 10 to 11)
		P ₂ (mm)	Fig. (No.)	Pitch (mm)	
AMMO-PACK		12.70	1	10.0/15.0	DQ
AMMO-PACK		19.05	2	22.5	DQ
REEL Ø 355mm		12.70	1	10.0/15.0	GY
REEL Ø 500mm		12.70	1	10.0/15.0	CK
REEL Ø 500mm		19.05	2	22.5/27.5	CK
Loose, short leads	4 ⁺²				AA
Loose, long leads (p<10mm)	17 ^{+1/-2}				Z3
Loose, long leads (p≥15mm)	30 ⁺⁵				40
	25 ^{+2/-1}				50

Note: Ammo-pack is the preferred packaging for taped version.

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

Typical applications: blocking, coupling, decoupling, by-passing, interference suppression in low voltage applications (i.e.: AUTOMOTIVE).

PRODUCT CODE: **R60**

Note: Special version, in compliance with DIN 44122 is available upon request.

Construction:

- **STACKED technology for pitch 10mm (Rated Voltage from 50 to 630Vdc)**
- **WOUND technology from pitch 10 to 27.5mm (Rated Voltage from 63 to 1000Vdc)**


Pitch (mm)	Box thickness (B) (mm)	Maximum dimensions (mm)		
		B max	H max	L max
10.0	All	B +0.2	H +0.1	L +0.2
15.0	<7.5	B +0.2	H +0.1	L +0.3
15.0	≥7.5	B +0.2	H +0.1	L +0.5
22.5	All	B +0.2	H +0.1	L +0.3
27.5	All	B +0.2	H +0.1	L +0.3
37.5	All	B +0.3	H +0.1	L +0.3

GENERAL TECHNICAL DATA

- Dielectric:** polyester film (polyethylene terephthalate).
- Plates:** aluminium layer deposited by evaporation under vacuum.
- Winding:** non-inductive type.
- Leads:** tinned wire.
- Protection:** plastic case, thermosetting resin filled. Box material is solvent resistant and flame retardant according to UL94.
- Marking:** Manufacturer's logo (if requested), capacitance, tolerance, D.C. rated voltage.
- Climatic category:** 55/105/56 IEC 60068-1
- Operating temperature range:** -55 to +105°C
Upper operating temperature of +125°C is allowed for a max.operating time of 1000h.

Related documents: IEC 60384-2

Winding scheme





R60

MKT Series

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

PRODUCT CODE: **R60**

STACKED VERSION

Rated Cap.	50Vdc/30Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
1.5 μF	4.0	9.0	13.0	10.0	30	3 E3	R60CF4150--6--
2.2 μF	4.0	9.0	13.0	10.0	30	3 E3	R60CF4220--6--
3.3 μF	5.0	11.0	13.0	10.0	30	3 E3	R60CF4330--6--
4.7 μF	6.0	12.0	13.0	10.0	30	3 E3	R60CF4470--6--
5.6 μF	6.0	12.0	13.0	10.0	30	3 E3	R60CF4560--6--

Rated Cap.	250Vdc/160Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
0.10 μF	4.0	9.0	13.0	10.0	150	75 E3	R60IF 3100--6--
0.15 μF	4.0	9.0	13.0	10.0	150	75 E3	R60IF 3150--6--
0.22 μF	5.0	11.0	13.0	10.0	150	75 E3	R60IF 3220--6--
0.33 μF	5.0	11.0	13.0	10.0	150	75 E3	R60IF 3330--6--
0.47 μF	6.0	12.0	13.0	10.0	150	75 E3	R60IF 3470--6--

Rated Cap.	63Vdc/40Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
1.0 μF	4.0	9.0	13.0	10.0	50	6.3 E3	R60DF4100--6--
1.5 μF	5.0	11.0	13.0	10.0	50	6.3 E3	R60DF4150--6--
2.2 μF	5.0	11.0	13.0	10.0	50	6.3 E3	R60DF4220--6--
3.3 μF	6.0	12.0	13.0	10.0	50	6.3 E3	R60DF4330--6--

Rated Cap.	400Vdc/200Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
0.033 μF	4.0	9.0	13.0	10.0	175	140 E3	R60MF2330--6--
0.047 μF	4.0	9.0	13.0	10.0	175	140 E3	R60MF2470--6--
0.068 μF	4.0	9.0	13.0	10.0	175	140 E3	R60MF2680--6--
0.10 μF	5.0	11.0	13.0	10.0	175	140 E3	R60MF3100--6--
0.15 μF	6.0	12.0	13.0	10.0	175	140 E3	R60MF3150--6--

Rated Cap.	100Vdc/63Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
0.33 μF	4.0	9.0	13.0	10.0	75	15 E3	R60EF3330--6--
0.47 μF	4.0	9.0	13.0	10.0	75	15 E3	R60EF3470--6--
0.68 μF	4.0	9.0	13.0	10.0	75	15 E3	R60EF3680--6--
1.0 μF	5.0	11.0	13.0	10.0	75	15 E3	R60EF4100--6--
1.5 μF	5.0	11.0	13.0	10.0	75	15 E3	R60EF4150--6--

Rated Cap.	630Vdc/220Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
0.010 μF	4.0	9.0	13.0	10.0	200	250 E3	R60PF2100--6--
0.015 μF	4.0	9.0	13.0	10.0	200	250 E3	R60PF2150--6--
0.022 μF	4.0	9.0	13.0	10.0	200	250 E3	R60PF2220--6--
0.033 μF	5.0	11.0	13.0	10.0	200	250 E3	R60PF2330--6--
0.047 μF	5.0	11.0	13.0	10.0	200	250 E3	R60PF2470--6--

Rated Cap.	160Vdc/90Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
0.22 μF	4.0	9.0	13.0	10.0	100	32 E3	R60GF3220--6--
0.33 μF	4.0	9.0	13.0	10.0	100	32 E3	R60GF3330--6--
0.47 μF	5.0	11.0	13.0	10.0	100	32 E3	R60GF3470--6--
0.68 μF	6.0	12.0	13.0	10.0	100	32 E3	R60GF3680--6--

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____

All dimensions are in mm.

Note: If the working voltage (V) is lower than the rated voltage (V_R), the capacitor may work at higher dv/dt. In this case the maximum value allowed is obtained multiplying the above value (see table dv/dt) with the ratio V_R/V.

The pulse characteristic K₀ depends on the voltage wave-form and in any case it cannot overcome the value given in the above table.

*Not suitable for across-the-line applications. Please refer to Interference Suppression Capacitors (page 145).



R60

MKT Series

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

PRODUCT CODE: R60

WOUND VERSION

Rated Cap.	63Vdc/40Vac Std dimensions					Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p				
0.68 μF	5.0	11.0	18.0	15.0	2.5	0.32 E3	R60DI 3680--3--	
1.0 μF	5.0	11.0	18.0	15.0	2.5	0.32 E3	R60DI 4100--3--	
1.5 μF	5.0	11.0	18.0	15.0	2.5	0.32 E3	R60DI 4150--3--	
2.2 μF	6.0	12.0	18.0	15.0	2.5	0.32 E3	R60DI 4220--3--	
3.3 μF	7.5	13.5	18.0	15.0	2.5	0.32 E3	R60DI 4330--3--	
3.3 μF	9.0	12.5	18.0	15.0	2.5	0.32 E3	R60DI 4330--L--	
4.7 μF	8.5	14.5	18.0	15.0	2.5	0.32 E3	R60DI 4470--3--	
4.7 μF	13.0	12.0	18.0	15.0	2.5	0.32 E3	R60DI 4470--L--	
6.8 μF	10.0	16.0	18.0	15.0	2.5	0.32 E3	R60DI 4680--3--	
3.3 μF	6.0	15.0	26.5	22.5	1.5	0.19 E3	R60DN4330--3--	
4.7 μF	7.0	16.0	26.5	22.5	1.5	0.19 E3	R60DN4470--3--	
6.8 μF	7.0	16.0	26.5	22.5	1.5	0.19 E3	R60DN4680--3--	
10.0 μF	8.5	17.0	26.5	22.5	1.5	0.19 E3	R60DN5100--3--	
15.0 μF	11.0	20.0	26.5	22.5	1.5	0.19 E3	R60DN5150--3--	
10.0 μF	9.0	17.0	32.0	27.5	1.0	0.13 E3	R60DR5100--3--	
15.0 μF	9.0	17.0	32.0	27.5	1.0	0.13 E3	R60DR5150--4--	
22.0 μF	11.0	20.0	32.0	27.5	1.0	0.13 E3	R60DR5220--4--	
33.0 μF	13.0	22.0	32.0	27.5	1.0	0.13 E3	R60DR5330--4--	
47.0 μF	14.0	28.0	32.0	27.5	1.0	0.13 E3	R60DR5470--4--	
68.0 μF	18.0	33.0	32.0	27.5	1.0	0.13 E3	R60DR5680--4--	
100.0 μF	22.0	37.0	32.0	27.5	1.0	0.13 E3	R60DR6100--0--	
22.0 μF	11.0	22.0	41.5	37.5	0.8	0.10 E3	R60DW5220--3--	
33.0 μF	11.0	22.0	41.5	37.5	0.8	0.10 E3	R60DW5330--4--	
47.0 μF	13.0	24.0	41.5	37.5	0.8	0.10 E3	R60DW5470--4--	
68.0 μF	19.0	32.0	41.5	37.5	0.8	0.10 E3	R60DW5680--3--	
100.0 μF	19.0	32.0	41.5	37.5	0.8	0.10 E3	R60DW6100--4--	
150.0 μF	20.0	40.0	41.5	37.5	0.8	0.10 E3	R60DW6150--0--	
220.0 μF	24.0	44.0	41.5	37.5	0.8	0.10 E3	R60DW6220--0--	

Rated Cap.	100Vdc/63Vac Std dimensions					Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p				
0.33 μF	5.0	11.0	18.0	15.0	3.0	0.6 E3	R60EI 3330--3--	
0.47 μF	5.0	11.0	18.0	15.0	3.0	0.6 E3	R60EI 3470--3--	
0.68 μF	5.0	11.0	18.0	15.0	3.0	0.6 E3	R60EI 3680--3--	
1.0 μF	5.0	11.0	18.0	15.0	3.0	0.6 E3	R60EI 4100--3--	
1.5 μF	7.5	13.5	18.0	15.0	3.0	0.6 E3	R60EI 4150--3--	
2.2 μF	8.5	14.5	18.0	15.0	3.0	0.6 E3	R60EI 4220--3--	
2.2 μF	9.0	12.5	18.0	15.0	3.0	0.6 E3	R60EI 4220--L--	
3.3 μF	10.0	16.0	18.0	15.0	3.0	0.6 E3	R60EI 4330--3--	
3.3 μF	13.0	12.0	18.0	15.0	3.0	0.6 E3	R60EI 4330--L--	
4.7 μF	11.0	19.0	18.0	15.0	3.0	0.6 E3	R60EI 4470--3--	
1.5 μF	6.0	15.0	26.5	22.5	2.0	0.4 E3	R60EN4150--3--	
2.2 μF	6.0	15.0	26.5	22.5	2.0	0.4 E3	R60EN4220--3--	
3.3 μF	7.0	16.0	26.5	22.5	2.0	0.4 E3	R60EN4330--3--	
4.7 μF	8.5	17.0	26.5	22.5	2.0	0.4 E3	R60EN4470--3--	
6.8 μF	10.0	18.5	26.5	22.5	2.0	0.4 E3	R60EN4680--3--	
10.0 μF	13.0	22.0	26.5	22.5	2.0	0.4 E3	R60EN5100--3--	
4.7 μF	9.0	17.0	32.0	27.5	1.5	0.3 E3	R60ER4470--3--	
6.8 μF	9.0	17.0	32.0	27.5	1.5	0.3 E3	R60ER4680--3--	
10.0 μF	9.0	17.0	32.0	27.5	1.5	0.3 E3	R60ER5100--4--	
15.0 μF	11.0	20.0	32.0	27.5	1.5	0.3 E3	R60ER5150--4--	
22.0 μF	13.0	22.0	32.0	27.5	1.5	0.3 E3	R60ER5220--4--	
33.0 μF	14.0	28.0	32.0	27.5	1.5	0.3 E3	R60ER5330--4--	
47.0 μF	18.0	33.0	32.0	27.5	1.5	0.3 E3	R60ER5470--4--	
68.0 μF	22.0	37.0	32.0	27.5	1.5	0.3 E3	R60ER5680--0--	
15.0 μF	11.0	22.0	41.5	37.5	1.0	0.2 E3	R60EW5150--4--	
22.0 μF	11.0	22.0	41.5	37.5	1.0	0.2 E3	R60EW5220--4--	
33.0 μF	13.0	24.0	41.5	37.5	1.0	0.2 E3	R60EW5330--4--	
47.0 μF	16.0	28.5	41.5	37.5	1.0	0.2 E3	R60EW5470--4--	
68.0 μF	19.0	32.0	41.5	37.5	1.0	0.2 E3	R60EW5680--5--	
100.0 μF	20.0	40.0	41.5	37.5	1.0	0.2 E3	R60EW6100--0--	
150.0 μF	24.0	44.0	41.5	37.5	1.0	0.2 E3	R60EW6150--0--	

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____
 All dimensions are in mm.

Rated Cap.	160Vdc/90Vac Std dimensions					Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p				
0.33 μF	5.0	11.0	18.0	15.0	9.0	2.90 E3	R60GI 3330--3--	
0.47 μF	5.0	11.0	18.0	15.0	9.0	2.90 E3	R60GI 3470--3--	
0.68 μF	5.0	11.0	18.0	15.0	9.0	2.90 E3	R60GI 3680--3--	
1.0 μF	7.5	13.5	18.0	15.0	9.0	2.90 E3	R60GI 4100--3--	
1.5 μF	8.5	14.5	18.0	15.0	9.0	2.90 E3	R60GI 4150--3--	
1.5 μF	9.0	12.5	18.0	15.0	9.0	2.90 E3	R60GI 4150--L--	
2.2 μF	10.0	16.0	18.0	15.0	9.0	2.90 E3	R60GI 4220--3--	
2.2 μF	13.0	12.0	18.0	15.0	9.0	2.90 E3	R60GI 4220--L--	
3.3 μF	11.0	19.0	18.0	15.0	9.0	2.90 E3	R60GI 4330--3--	
1.5 μF	6.0	15.0	26.5	22.5	5.5	1.70 E3	R60GN4150--3--	
2.2 μF	7.0	16.0	26.5	22.5	5.5	1.70 E3	R60GN4220--3--	
3.3 μF	8.5	17.0	26.5	22.5	5.5	1.70 E3	R60GN4330--3--	
4.7 μF	11.0	20.0	26.5	22.5	5.5	1.70 E3	R60GN4470--3--	
6.8 μF	13.0	22.0	26.5	22.5	5.5	1.70 E3	R60GN4680--3--	
3.3 μF	9.0	17.0	32.0	27.5	3.0	0.96 E3	R60GR4330--3--	
4.7 μF	9.0	17.0	32.0	27.5	3.0	0.96 E3	R60GR4470--3--	
6.8 μF	9.0	17.0	32.0	27.5	3.0	0.96 E3	R60GR4680--4--	
10.0 μF	9.0	17.0	32.0	27.5	3.0	0.96 E3	R60GR5100--4--	
15.0 μF	11.0	20.0	32.0	27.5	3.0	0.96 E3	R60GR5150--4--	
22.0 μF	13.0	22.0	32.0	27.5	3.0	0.96 E3	R60GR4470--4--	
33.0 μF	14.0	28.0	32.0	27.5	3.0	0.96 E3	R60GR5330--0--	
47.0 μF	18.0	33.0	32.0	27.5	3.0	0.96 E3	R60GR5470--0--	
68.0 μF	22.0	37.0	32.0	27.5	3.0	0.96 E3	R60GR5680--0--	
10.0 μF	11.0	22.0	41.5	37.5	2.0	0.64 E3	R60GW5100--3--	
15.0 μF	11.0	22.0	41.5	37.5	2.0	0.64 E3	R60GW5150--4--	
22.0 μF	11.0	22.0	41.5	37.5	2.0	0.64 E3	R60GW5220--4--	
33.0 μF	13.0	24.0	41.5	37.5	2.0	0.64 E3	R60GW5330--4--	
47.0 μF	16.0	28.5	41.5	37.5	2.0	0.64 E3	R60GW5470--4--	
68.0 μF	19.0	32.0	41.5	37.5	2.0	0.64 E3	R60GW5680--0--	
100.0 μF	20.0	40.0	41.5	37.5	2.0	0.64 E3	R60GW6100--0--	
150.0 μF	30.0	45.0	41.5	37.5	2.0	0.64 E3	R60GW6150--0--	

Rated Cap.	250Vdc/160Vac Std dimensions					Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p				
0.10 μF	5.0	11.0	18.0	15.0	12	6.0 E3	R60II 3100--3--	
0.15 μF	5.0	11.0	18.0	15.0	12	6.0 E3	R60II 3150--3--	
0.22 μF	5.0	11.0	18.0	15.0	12	6.0 E3	R60II 3220--3--	
0.33 μF	5.0	11.0	18.0	15.0	12	6.0 E3	R60II 3330--3--	
0.47 μF	6.0	12.0	18.0	15.0	12	6.0 E3	R60II 3470--3--	
0.68 μF	7.5	13.5	18.0	15.0	12	6.0 E3	R60II 3680--3--	
0.68 μF	9.0	12.5	18.0	15.0	12	6.0 E3	R60II 3680--L--	
1.0 μF	8.5	14.5	18.0	15.0	12	6.0 E3	R60II 4100--3--	
1.0 μF	13.0	12.0	18.0	15.0	12	6.0 E3	R60II 4100--L--	
1.5 μF	10.0	16.0	18.0	15.0	12	6.0 E3	R60II 4150--3--	
0.47 μF	6.0	15.0	26.5	22.5	8	4.0 E3	R60IN 3470--3--	
0.68 μF	6.0	15.0	26.5	22.5	8	4.0 E3	R60IN 3680--3--	
1.0 μF	6.0	15.0	26.5	22.5	8	4.0 E3	R60IN 4100--3--	
1.5 μF	7.0	16.0	26.5	22.5	8	4.0 E3	R60IN 4150--3--	
2.2 μF	10.0	18.5	26.5	22.5	8	4.0 E3	R60IN 4220--3--	
3.3 μF	11.0	20.0	26.5	22.5	8	4.0 E3	R60IN 4330--3--	
1.5 μF	9.0	17.0	32.0	27.5	5	2.5 E3	R60IR 4150--3--	
2.2 μF	9.0	17.0	32.0	27.5	5	2.5 E3	R60IR 4220--3--	
3.3 μF	9.0	17.0	32.0	27.5	5	2.5 E3	R60IR 4330--4--	
4.7 μF	9.0	17.0	32.0	27.5	5	2.5 E3	R60IR 4470--4--	
6.8 μF	11.0	20.0	32.0	27.5	5	2.5 E3	R60IR 4680--4--	
10.0 μF	13.0	22.0	32.0	27.5	5	2.5 E3	R60IR 5100--4--	
15.0 μF	14.0	28.0	32.0	27.5	5	2.5 E3	R60IR 5150--4--	
22.0 μF	18.0	33.0	32.0	27.5	5	2.5 E3	R60IR 5220--0--	
33.0 μF	22.0	37.0	32.0	27.5	5	2.5 E3	R60IR 5330--0--	
4.7 μF	11.0	22.0	41.5	37.5	4	2.0 E3	R60IW 4470--3--	
6.8 μF	11.0	22.0	41.5	37.5	4	2.0 E3	R60IW 4680--4--	
10.0 μF	11.0	22.0	41.5	37.5	4	2.0 E3	R60IW 5100--4--	
15.0 μF	13.0	24.0	41.5	37.5	4	2.0 E3	R60IW 5150--4--	
22.0 μF	16.0	28.5	41.5	37.5	4	2.0 E3	R60IW 5220--4--	
33.0 μF	19.0	32.0	41.5	37.5	4	2.0 E3	R60IW 5330--4--	
47.0 μF	20.0	40.0	41.5	37.5	4	2.0 E3	R60IW 5470--0--	
68.0 μF	24.0	44.0	41.5	37.5	4	2.0 E3	R60IW 5680--0--	

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____

Note: If the working voltage (V) is lower than the rated voltage (V_R), the capacitor may work at higher dv/dt. In this case the maximum value allowed is obtained multiplying the above value (see table dv/dt) with the ratio V_R/V.
 The pulse characteristic K₀ depends on the voltage wave-form and in any case it cannot overcome the value given in the above table.



R60

MKT Series

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

PRODUCT CODE: **R60**

WOUND VERSION

Rated Cap.	400Vdc/200Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
0.015 μF	4.0	9.0	13.0	10.0	30.0	24.0 E3	R60MF2150--3--
0.022 μF	4.0	9.0	13.0	10.0	30.0	24.0 E3	R60MF 2220--3--
0.033 μF	4.0	9.0	13.0	10.0	30.0	24.0 E3	R60MF 2330--3--
0.047 μF	4.0	9.0	13.0	10.0	30.0	24.0 E3	R60MF 2470--3--
0.068 μF	4.0	9.0	13.0	10.0	30.0	24.0 E3	R60MF 2680--4--
0.068 μF	5.0	11.0	13.0	10.0	30.0	24.0 E3	R60MF 2680--3--
0.10 μF	5.0	11.0	13.0	10.0	30.0	24.0 E3	R60MF 3100--4--
0.10 μF	6.0	12.0	13.0	10.0	30.0	24.0 E3	R60MF 3100--3--
0.15 μF	6.0	12.0	13.0	10.0	30.0	24.0 E3	R60MF 3150--3--
0.022 μF	5.0	11.0	18.0	15.0	20.0	16.0 E3	R60MI 2220--3--
0.047 μF	5.0	11.0	18.0	15.0	20.0	16.0 E3	R60MI 2470--3--
0.068 μF	5.0	11.0	18.0	15.0	20.0	16.0 E3	R60MI 2680--3--
0.10 μF	5.0	11.0	18.0	15.0	20.0	16.0 E3	R60MI 3100--3--
0.15 μF	5.0	11.0	18.0	15.0	20.0	16.0 E3	R60MI 3150--3--
0.22 μF	5.0	11.0	18.0	15.0	20.0	16.0 E3	R60MI 3220--4--
0.22 μF	6.0	12.0	18.0	15.0	20.0	16.0 E3	R60MI 3220--3--
0.33 μF	7.5	13.5	18.0	15.0	20.0	16.0 E3	R60MI 3330--3--
0.33 μF	9.0	12.5	18.0	15.0	20.0	16.0 E3	R60MI 3330--L--
0.47 μF	7.5	13.5	18.0	15.0	20.0	16.0 E3	R60MI 3470--4--
0.47 μF	8.5	14.5	18.0	15.0	20.0	16.0 E3	R60MI 3470--3--
0.47 μF	9.0	12.5	18.0	15.0	20.0	16.0 E3	R60MI 3470--L1-
0.47 μF	13.0	12.0	18.0	15.0	20.0	16.0 E3	R60MI 3470--L--
0.68 μF	10.0	16.0	18.0	15.0	20.0	16.0 E3	R60MI 3680--4--
0.68 μF	11.0	19.0	18.0	15.0	20.0	16.0 E3	R60MI 3680--3--
0.68 μF	13.0	12.0	18.0	15.0	20.0	16.0 E3	R60MI 3680--L--
1.0 μF	11.0	19.0	18.0	15.0	20.0	16.0 E3	R60MI 4100--3--
0.22 μF	6.0	15.0	26.5	22.5	10.0	8.0 E3	R60MN3220--3--
0.33 μF	6.0	15.0	26.5	22.5	10.0	8.0 E3	R60MN3330--3--
0.47 μF	6.0	15.0	26.5	22.5	10.0	8.0 E3	R60MN3470--3--
0.68 μF	6.0	15.0	26.5	22.5	10.0	8.0 E3	R60MN3680--4--
0.68 μF	7.0	16.0	26.5	22.5	10.0	8.0 E3	R60MN3680--3--
1.0 μF	8.5	17.0	26.5	22.5	10.0	8.0 E3	R60MN4100--4--
1.0 μF	10.0	18.5	26.5	22.5	10.0	8.0 E3	R60MN4100--3--
1.5 μF	10.0	18.5	26.5	22.5	10.0	8.0 E3	R60MN4150--4--
1.5 μF	11.0	20.0	26.5	22.5	10.0	8.0 E3	R60MN4150--3--
2.2 μF	13.0	22.0	26.5	22.5	10.0	8.0 E3	R60MN4220--3--
0.68 μF	9.0	17.0	32.0	27.5	8.5	3.4 E3	R60MR3680--3--
1.0 μF	9.0	17.0	32.0	27.5	8.5	3.4 E3	R60MR4100--3--
1.5 μF	9.0	17.0	32.0	27.5	8.5	3.4 E3	R60MR4150--4--
2.2 μF	11.0	20.0	32.0	27.5	8.5	3.4 E3	R60MR4220--4--
3.3 μF	13.0	22.0	32.0	27.5	8.5	3.4 E3	R60MR4330--4--
4.7 μF	14.0	28.0	32.0	27.5	8.5	3.4 E3	R60MR4470--4--
6.8 μF	18.0	33.0	32.0	27.5	8.5	3.4 E3	R60MR4680--4--
10.0 μF	22.0	37.0	32.0	27.5	8.5	3.4 E3	R60MR5100--4--
3.3 μF	11.0	22.0	41.5	37.5	6.0	2.4 E3	R60MW4330--3--
4.7 μF	11.0	22.0	41.5	37.5	6.0	2.4 E3	R60MW4470--4--
6.8 μF	13.0	24.0	41.5	37.5	6.0	2.4 E3	R60MW4680--4--
10.0 μF	16.0	28.5	41.5	37.5	6.0	2.4 E3	R60MW5100--4--
15.0 μF	24.0	44.0	41.5	37.5	6.0	2.4 E3	R60MW5150--3--
22.0 μF	24.0	44.0	41.5	37.5	6.0	2.4 E3	R60MW5220--4--
33.0 μF	30.0	45.0	41.5	37.5	6.0	2.4 E3	R60MW5330--4--

Rated Cap.	630Vdc/220*Vac Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
4700 pF	4.0	9.0	13.0	10.0	40	50 E3	R60PF 1470--3--
6800 pF	4.0	9.0	13.0	10.0	40	50 E3	R60PF 1680--3--
0.010 μF	4.0	9.0	13.0	10.0	40	50 E3	R60PF 2100--3--
0.015 μF	4.0	9.0	13.0	10.0	40	50 E3	R60PF 2150--3--
0.022 μF	4.0	9.0	13.0	10.0	40	50 E3	R60PF 2220--4--
0.022 μF	5.0	11.0	13.0	10.0	40	50 E3	R60PF 2220--3--
0.033 μF	5.0	11.0	13.0	10.0	40	50 E3	R60PF 2330--4--
0.033 μF	6.0	12.0	13.0	10.0	40	50 E3	R60PF 2330--3--
0.047 μF	6.0	12.0	13.0	10.0	40	50 E3	R60PF 2470--3--
0.033 μF	5.0	11.0	18.0	15.0	25	31 E3	R60PI 2330--3--
0.047 μF	5.0	11.0	18.0	15.0	25	31 E3	R60PI 2470--3--
0.068 μF	5.0	11.0	18.0	15.0	25	31 E3	R60PI 2680--4--
0.068 μF	6.0	12.0	18.0	15.0	25	31 E3	R60PI 2680--3--
0.10 μF	6.0	12.0	18.0	15.0	25	31 E3	R60PI 3100--4--
0.10 μF	7.5	13.5	18.0	15.0	25	31 E3	R60PI 3100--3--
0.10 μF	9.0	12.5	18.0	15.0	25	31 E3	R60PI 3100--L--
0.15 μF	7.5	13.5	18.0	15.0	25	31 E3	R60PI 3150--4--
0.15 μF	8.5	14.5	18.0	15.0	25	31 E3	R60PI 3150--3--
0.22 μF	8.5	14.5	18.0	15.0	25	31 E3	R60PI 3220--4--
0.22 μF	10.0	16.0	18.0	15.0	25	31 E3	R60PI 3220--3--
0.33 μF	10.0	16.0	18.0	15.0	25	31 E3	R60PI 3330--3--
0.10 μF	6.0	15.0	26.5	22.5	12	15 E3	R60PN3100--3--
0.15 μF	6.0	15.0	26.5	22.5	12	15 E3	R60PN3150--3--
0.22 μF	6.0	15.0	26.5	22.5	12	15 E3	R60PN3220--4--
0.22 μF	7.0	16.0	26.5	22.5	12	15 E3	R60PN3220--3--
0.33 μF	7.0	16.0	26.5	22.5	12	15 E3	R60PN3330--5--
0.33 μF	8.5	17.0	26.5	22.5	12	15 E3	R60PN3330--4--
0.33 μF	10.0	18.5	26.5	22.5	12	15 E3	R60PN3330--3--
0.47 μF	10.0	18.5	26.5	22.5	12	15 E3	R60PN3470--4--
0.47 μF	11.0	20.0	26.5	22.5	12	15 E3	R60PN3470--3--
0.68 μF	11.0	20.0	26.5	22.5	12	15 E3	R60PN3680--4--
0.68 μF	13.0	22.0	26.5	22.5	12	15 E3	R60PN3680--3--
0.33 μF	9.0	17.0	32.0	27.5	10	12 E3	R60PR3330--3--
0.47 μF	9.0	17.0	32.0	27.5	10	12 E3	R60PR3470--4--
0.68 μF	11.0	20.0	32.0	27.5	10	12 E3	R60PR3680--4--
1.0 μF	11.0	20.0	32.0	27.5	10	12 E3	R60PR4100--5--
1.5 μF	18.0	33.0	32.0	27.5	10	12 E3	R60PR4150--3--
2.2 μF	18.0	33.0	32.0	27.5	10	12 E3	R60PR4220--4--
3.3 μF	22.0	37.0	32.0	27.5	10	12 E3	R60PR4330--4--
4.7 μF	22.0	37.0	32.0	27.5	10	12 E3	R60PR4470--4--
1.0 μF	11.0	22.0	41.5	37.5	8	9.6 E3	R60PW4100--3--
1.5 μF	11.0	22.0	41.5	37.5	8	9.6 E3	R60PW4150--4--
2.2 μF	13.0	24.0	41.5	37.5	8	9.6 E3	R60PW4220--4--
3.3 μF	16.0	28.5	41.5	37.5	8	9.6 E3	R60PW4330--4--
4.7 μF	19.0	32.0	41.5	37.5	8	9.6 E3	R60PW4470--4--
6.8 μF	20.0	40.0	41.5	37.5	8	9.6 E3	R60PW4680--0--
10.0 μF	24.0	44.0	41.5	37.5	8	9.6 E3	R60PW5100--4--

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____

All dimensions are in mm.

Note: If the working voltage (V) is lower than the rated voltage (V_R), the capacitor may work at higher dv/dt. In this case the maximum value allowed is obtained multiplying the above value (see table dv/dt) with the ratio V_R/V.
 The pulse characteristic K₀ depends on the voltage wave-form and in any case it cannot overcome the value given in the above table.

* Not suitable for across-the-line applications. Please refer to Interference Suppression Capacitors (page 145).



R60

MKT Series

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

PRODUCT CODE: **R60**

WOUND VERSION

Rated Cap.	1000Vdc/250Vac* Std dimensions				Max dv/dt (V/μs)	Max K ₀ (V ² /μs)	Part Number
	B	H	L	p			
1000 pF	4.0	9.0	13.0	10.0	60	120 E3	R60QF 1100--0--
1500 pF	4.0	9.0	13.0	10.0	60	120 E3	R60QF 1150--0--
2200 pF	4.0	9.0	13.0	10.0	60	120 E3	R60QF 1220--0--
3300 pF	4.0	9.0	13.0	10.0	60	120 E3	R60QF 1330--0--
4700 pF	5.0	11.0	13.0	10.0	60	120 E3	R60QF 1470--0--
6800 pF	6.0	12.0	13.0	10.0	60	120 E3	R60QF 1680--0--
0.010 μF	5.0	11.0	18.0	15.0	30	60 E3	R60QI 2100--0--
0.015 μF	5.0	11.0	18.0	15.0	30	60 E3	R60QI 2150--3--
0.022 μF	6.0	12.0	18.0	15.0	30	60 E3	R60QI 2220--3--
0.033 μF	7.5	13.5	18.0	15.0	30	60 E3	R60QI 2330--3--
0.033 μF	9.0	12.5	18.0	15.0	30	60 E3	R60QI 2330--L--
0.047 μF	10.0	16.0	18.0	15.0	30	60 E3	R60QI 2470--0--
0.047 μF	13.0	12.0	18.0	15.0	30	60 E3	R60QI 2470--L--
0.068 μF	11.0	19.0	18.0	15.0	30	60 E3	R60QI 2680--0--
0.033 μF	6.0	15.0	26.5	22.5	15	30 E3	R60QN2330--0--
0.047 μF	6.0	15.0	26.5	22.5	15	30 E3	R60QN2470--0--
0.068 μF	7.0	16.0	26.5	22.5	15	30 E3	R60QN2680--3--
0.10 μF	8.5	17.0	26.5	22.5	15	30 E3	R60QN3100--3--
0.15 μF	13.0	22.0	26.5	22.5	15	30 E3	R60QN3150--0--
0.15 μF	9.0	17.0	32.0	27.5	12	24 E3	R60QR3150--3--
0.22 μF	9.0	17.0	32.0	27.5	12	24 E3	R60QR3220--4--
0.33 μF	11.0	20.0	32.0	27.5	12	24 E3	R60QR3330--4--
0.47 μF	13.0	22.0	32.0	27.5	12	24 E3	R60QR3470--4--
0.68 μF	14.0	28.0	32.0	27.5	12	24 E3	R60QR3680--4--
1.00 μF	18.0	33.0	32.0	27.5	12	24 E3	R60QR4100--4--
1.50 μF	22.0	37.0	32.0	27.5	12	24 E3	R60QR4150--4--
0.47 μF	11.0	22.0	41.5	37.5	10	20 E3	R60QW3470--3--
0.68 μF	11.0	22.0	41.5	37.5	10	20 E3	R60QW3680--4--
1.00 μF	13.0	24.0	41.5	37.5	10	20 E3	R60QW4100--4--
1.50 μF	16.0	28.5	41.5	37.5	10	20 E3	R60QW4150--4--
2.20 μF	19.0	32.0	41.5	37.5	10	20 E3	R60QW4220--3--
3.30 μF	24.0	44.0	41.5	37.5	10	20 E3	R60QW4330--0--
4.70 μF	30.0	45.0	41.5	37.5	10	20 E3	R60QW4470--4--

All dimensions are in mm.

Note 1: If the working voltage (V) is lower than the rated voltage (V_R), the capacitor may work at higher dv/dt. In this case the maximum value allowed is obtained multiplying the above value (see table dv/dt) with the ratio V_R/V. The pulse characteristic K₀ depends on the voltage wave-form and in any case it cannot overcome the value given in the above table.

Note 2: Rated voltages higher than 1000Vdc are available upon request.

* Not suitable for across-the-line applications. Please refer to Interference Suppression Capacitors (page 151).

Mechanical version and packaging (Table1) _____
 Internal use _____
 Tolerance: J (±5%); K (±10%); M (±20%) _____

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**
PRODUCT CODE: **R60****ELECTRICAL CHARACTERISTICS**

Rated voltage (V_R): 50Vdc - 63Vdc - 100Vdc - 160Vdc
- 250Vdc - 400Vdc - 630Vdc - 1000Vdc .

Rated temperature (T_R): +85°C

Temperature derated voltage:

for temperatures between +85°C and +125°C

a decreasing factor of 1.25% per degree °C on the rated voltage V_R (d.c. and a.c.) has to be applied.

Capacitance range: 1000pF to 220 μ F

Capacitance values:

E6 series (IEC 60063 Norm).

Capacitance tolerances (measured at 1 kHz):

$\pm 5\%$ (J); $\pm 10\%$ (K); $\pm 20\%$ (M).

Total self-inductance (L): (lead length ~2mm)

Pitch (mm)	10	15	22.5	27.5	37.5
L(nH) \approx	9	10	18	18	22

Dissipation factor (DF):

$\text{tg}\delta$ 10^{-4} at +25°C $\pm 5^\circ\text{C}$

kHz	C $\leq 1\mu\text{F}$	C $> 1\mu\text{F}$
1	≤ 100	≤ 100
10	≤ 150	

Insulation resistance:

Test conditions

Temperature: +25°C $\pm 5^\circ\text{C}$

Voltage charge time: 1 min

Voltage charge: 50 Vdc for $V_R < 100$ Vdc
100 Vdc for $V_R \geq 100$ Vdc

Performance

For $V_R \leq 100$ Vdc

≥ 3750 M Ω for C $\leq 0.33\mu\text{F}$ (50000 M Ω)*

≥ 1250 s for C $> 0.33\mu\text{F}$ (5000 s)*

For $V_R > 100$ Vdc

≥ 30000 M Ω for C $\leq 0.33\mu\text{F}$ (50000 M Ω)*

≥ 10000 s for C $> 0.33\mu\text{F}$ (17000 s)*

*Typical value

Test voltage between terminations:

$1.6 \times V_R$ applied for 2 s at +25°C $\pm 5^\circ\text{C}$

TEST METHOD AND PERFORMANCE

Damp heat, steady state:

Test conditions

Temperature: +40°C $\pm 2^\circ\text{C}$

Relative humidity (RH): 93% $\pm 2\%$

Test duration: 56 days

Performance

Capacitance change $|\Delta C/C|$: $\leq 5\%$

DF change ($\Delta \text{tg}\delta$): $\leq 50 \times 10^{-4}$ at 1kHz

Insulation resistance: $\geq 50\%$ of initial limit.

Endurance:

Test conditions

Temperature: +105°C $\pm 2^\circ\text{C}$

Test duration: 2000 h

Voltage applied: $1.25 \times V_C$

Performance

Capacitance change $|\Delta C/C|$: $\leq 5\%$

DF change ($\Delta \text{tg}\delta$): $\leq 50 \times 10^{-4}$ at 10kHz for C $\leq 1\mu\text{F}$
 $\leq 30 \times 10^{-4}$ at 1kHz for C $> 1\mu\text{F}$

Insulation resistance: $\geq 50\%$ of initial limit.

Resistance to soldering heat:

Test conditions

Solder bath temperature: +260°C $\pm 5^\circ\text{C}$

Dipping time (with heat screen): 10 s ± 1 s

Performance

Capacitance change $|\Delta C/C|$: $\leq 2\%$

DF change ($\Delta \text{tg}\delta$): $\leq 50 \times 10^{-4}$ at 10kHz for C $\leq 1\mu\text{F}$
 $\leq 30 \times 10^{-4}$ at 1kHz for C $> 1\mu\text{F}$

Insulation resistance: \geq initial limit.

Long term stability (after two years):

Storage: standard environmental conditions (see page 12).

Performance

Capacitance change $|\Delta C/C|$: $\leq 3\%$ for C $\leq 0.1\mu\text{F}$
 $\leq 2\%$ for C $> 0.1\mu\text{F}$

RELIABILITY:

Reference MIL HDB 217

Application conditions:

Temperature: +40°C $\pm 2^\circ\text{C}$

Voltage: $0.5 \times V_R$

Failure rate: ≤ 5 FIT

(1 FIT = 1×10^{-9} failures/componentsxh)

Failure criteria:

Short or open circuit

Capacitance change $|\Delta C/C|$: $> 10\%$








DF change ($\Delta \text{tg}\delta$): $> 2 \times$ initial limit.

Insulation resistance: $< 0.005 \times$ initial limit.

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

PRODUCT CODE: R60

MAX. VOLTAGE (Vr.m.s.) VERSUS FREQUENCY (sinusoidal wave-form / Th ≤ 40°C)










Note: p (pitch) in mm.

**METALLIZED POLYESTER FILM CAPACITOR
D.C. MULTIPURPOSE APPLICATIONS**

PRODUCT CODE: R60

MAX. CURRENT ($I_{r.m.s.}$) VERSUS FREQUENCY (sinusoidal wave-form / $T_h \leq 40^\circ\text{C}$)



Note: p (pitch) in mm.

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.