

Metallized Polypropylene (PP) RFI-Capacitors Class Y2
in PCM 10 mm to 37.5 mm. Capacitances from 1000 pF to 1.0 μ F.
Rated Voltage 300 VAC.

Special Features

- Reliable self-healing
- High degree of interference suppression due to good attenuation and low ESR
- AEC-Q200 qualified
- According to RoHS 2015/863/EU

Typical Applications

Class Y2 RFI applications to meet EMC regulations

- Capacitors connected to the mains between phase or neutral and earthed casing
- By-passing of the basic or supplementary insulation, pulse peak voltage ≤ 5 kV

Construction


Dielectric:

Polypropylene (PP) film

Capacitor electrodes:

Vacuum-deposited

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

Terminations:

Tinned wire.

Marking:

Colour: Red. Marking: Black.

Electrical Data

Capacitance range: 1000 pF to 1.0 μ F

Rated voltage: 300 VAC

Continuous DC voltage* (general guide): ≤ 1000 V

Capacitance tolerances:

$\pm 20\%$, $\pm 10\%$, $\pm 5\%$

Operating temperature range:

-55°C to $+105^\circ\text{C}$

Climatic test category:

55/105/56 in accordance with IEC

Passive flammability class:

B for capacitors with $V > 1750$ mm³

C for capacitors with $V \leq 1750$ mm³

Dissipation factors at $+20^\circ\text{C}$: $\tan \delta$

at f	$C \leq 0.1 \mu\text{F}$	$0.1 \mu\text{F} < C \leq 1.0 \mu\text{F}$
1 kHz	$\leq 18 \times 10^{-4}$	$\leq 20 \times 10^{-4}$
10 kHz	$\leq 20 \times 10^{-4}$	$\leq 60 \times 10^{-4}$
100 kHz	$\leq 100 \times 10^{-4}$	–

Insulation resistance at $+20^\circ\text{C}$:

$C \leq 0.33 \mu\text{F}$: $\geq 1.5 \times 10^4 \text{ M}\Omega$

$C > 0.33 \mu\text{F}$: $\geq 5000 \text{ sec (M}\Omega \times \mu\text{F)}$

Measuring voltage: 100 V/1 min.

Test specifications:

In accordance with IEC 60384-14

Maximum pulse rise time:

100 V/ μsec for pulses equal to a voltage

amplitude with $\sqrt{2} \times 300 \text{ VAC} = 425 \text{ V}$

according to IEC 60384-14

Test voltage: 2700 VDC, 2 sec.

Reliability:

Operational life > 300000 hours

Failure rate < 2 fit ($0.5 \times U_r$ and 40°C)

Approvals:

Country	Authority	Specification	Symbol	Approval-No.
Germany	VDE	IEC 60384-14/4		40008997
USA/Canada	UL	UL 60384-14 CAN/CSA-E60384-14		E 134915

Mechanical Tests

Pull test on pins: 10 N in direction of pins according to IEC 60068-2-21

Vibration: 6 hours at 10...2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

Low air density: 1 kPa = 10 mbar in accordance with IEC 60068-2-13

Bump test: 4000 bumps at 390 m/sec² in accordance with IEC 60068-2-29

Packing

Available taped and reeled.

Detailed taping information and graphs at the end of the catalogue.

* If safety-approved EMI suppression capacitors are operated with a DC voltage being above the specified AC voltage rating the given approvals are no longer valid (IEC 60384-14).

Furthermore the permissible pulse rise time du/dt (F_{max}) will be subject to a reduction according to

$$F_{\text{max}} = F_r \times \sqrt{2} \times \text{UAC} / \text{UDC}$$

if the DC operating voltage UDC is higher than $\sqrt{2} \times \text{UAC}$

For further details and graphs please refer to Technical Information.

Continuation


General Data

Capacitance	W	H	300 VAC* L	PCM**	Part number
1000 pF	4	9.5	13	10	MKY22W11003D00
1200 "	4	9.5	13	10	MKY22W11203D00
1500 "	4	9.5	13	10	MKY22W11503D00
1800 "	4	9.5	13	10	MKY22W11803D00
2200 "	4	9.5	13	10	MKY22W12203D00
2700 "	4	9.5	13	10	MKY22W12703D00
3300 "	4	9.5	13	10	MKY22W13303D00
3900 "	4	9.5	13	10	MKY22W13903D00
4700 "	5	11	13	10	MKY22W14703F00
5600 "	5	11	13	10	MKY22W15603F00
6800 "	6	12.5	13	10	MKY22W16803H00
	5	11	18	15	MKY22W16804B00
8200 "	6	12.5	13	10	MKY22W18203H00
	5	11	18	15	MKY22W18204B00
0.01 µF	8	12	13	10	MKY22W21003I00
	5	11	18	15	MKY22W21004B00
0.012 "	5	11	18	15	MKY22W21204B00
0.015 "	5	11	18	15	MKY22W21504B00
0.018 "	5	11	18	15	MKY22W21804B00
0.022 "	6	12.5	18	15	MKY22W22204C00
0.027 "	6	12.5	18	15	MKY22W22704C00
0.033 "	8	15	18	15	MKY22W23304F00
0.039 "	8	15	18	15	MKY22W23904F00
0.047 "	8	15	18	15	MKY22W24704F00
0.056 "	8	15	18	15	MKY22W25604F00
0.068 "	9	16	18	15	MKY22W26804J00
	6	15	26.5	22.5	MKY22W26805B00
0.082 "	7	16.5	26.5	22.5	MKY22W28205D00

* f = 50/60 Hz

** PCM = Printed circuit module = pin spacing

Dims. in mm.



d = 0.6 Ø if PCM = 10
d = 0.8 Ø if PCM = 15 - 22.5

Part number completion:	
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 151.	

Rights reserved to amend design data without prior notification.

Continuation page 91

Continuation


General Data

Capacitance	W	H	300 VAC* L	PCM**	Part number
0.1 μ F	7	16.5	26.5	22.5	MKY22W31005D00
0.12 "	8.5	18.5	26.5	22.5	MKY22W31205F00
0.15 "	8.5	18.5	26.5	22.5	MKY22W31505F00
	9	19	31.5	27.5	MKY22W31506A00
0.18 "	10.5	19	26.5	22.5	MKY22W31805G00
	9	19	31.5	27.5	MKY22W31806A00
0.22 "	11	21	26.5	22.5	MKY22W32205I00
	9	19	31.5	27.5	MKY22W32206A00
0.27 "	11	21	31.5	27.5	MKY22W32706B00
0.33 "	11	21	31.5	27.5	MKY22W33306B00
	13	24	41.5	37.5	MKY22W33307C00
0.39 "	13	24	31.5	27.5	MKY22W33906D00
	13	24	41.5	37.5	MKY22W33907C00
0.47 "	15	26	31.5	27.5	MKY22W34706F00
	13	24	41.5	37.5	MKY22W34707C00
0.56 "	15	26	31.5	27.5	MKY22W35606F00
	13	24	41.5	37.5	MKY22W35607C00
	15	26	41.5	37.5	MKY22W35607D00
0.68 "	17	29	31.5	27.5	MKY22W36806G00
	15	26	41.5	37.5	MKY22W36807D00
	17	29	41.5	37.5	MKY22W36807E00
0.82 "	17	34.5	31.5	27.5	MKY22W38206I00
	17	29	41.5	37.5	MKY22W38207E00
	19	32	41.5	37.5	MKY22W38207F00
1.0 μ F	20	39.5	31.5	27.5	MKY22W41006J00
	17	29	41.5	37.5	MKY22W41007E00
	20	39.5	41.5	37.5	MKY22W41007G00

* f = 50/60 Hz

** PCM = Printed circuit module = pin spacing


Dims. in mm.



d = 0.8 $\varnothing$ if PCM ≤ 27.5
d = 1.0 $\varnothing$ if PCM = 37.5

Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J
Packing: bulk = S
Pin length: 6-2 = SD
Taped version see page 151.




Rights reserved to amend design data without prior notification.

AC current graphs see page 88


Continuation

Permissible AC current in relation to frequency at 10° C internal temperature rise (general guide).



WIMA MKP-Y2

Permissible AC current in relation to frequency at 10° C internal temperature rise (general guide).



Technical information and general data see page 89

Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating: $T_{\max.} \leq 125^{\circ}\text{C}$
soldering: $T_{\max.} \leq 135^{\circ}\text{C}$

Polypropylene: preheating: $T_{\max.} \leq 100^{\circ}\text{C}$
soldering: $T_{\max.} \leq 110^{\circ}\text{C}$

Single wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$

Dwell time: $t < 5\text{ sec}$


Double wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$

Dwell time: $\sum t < 5\text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.

Wave soldering



Typical temperature/time graph for double wave soldering

WIMA Quality and Environmental Philosophy

ISO 9001:2015 Certification

ISO 9001:2015 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2015 of our factories certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- Testing as per customer requirements

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- adhesive tapes made of plastic
- metal clips

RoHS Compliance

According to the RoHS Directive 2015/863/EU as amended from time to time certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has re-frained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2015/863/EU

WIMA capacitors are lead free in accordance with RoHS 2015/863/EU

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

Typical Dimensions for Taping Configuration




Diagram 1:
PCM 2.5/5/7.5mm




Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm

*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	PCM 5 taping	PCM 7.5 taping	PCM 10 taping*	PCM 15 taping*	PCM 22.5 taping	PCM 27.5 taping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W ₀	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W ₁	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W ₂	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D ₀	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	*38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P ₀	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch
Feed hole centre to pin	P ₁	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P ₂	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H ▲	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H ₁	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 24.5 to 31.5	H+H _{component} < H ₁ 25.0 to 31.5	H+H _{component} < H ₁ 26.0 to 37.0	H+H _{component} < H ₁ 30.0 to 43.0	H+H _{component} < H ₁ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 ^{+0.8} _{-0.2}	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	*0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	*0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2
Package (see also page 152)	▲	ROLL/AMMO			AMMO			
		REEL Ø 360 max. Ø 30 ±1	B 52 ±2 58 ±2 depending on comp. dimensions		REEL Ø 360 max. Ø 30 ±1	B 52 ±2 58 ±2 or 66 ±2	REEL Ø 500 max. Ø 25 ±1	B 54 ±2 60 ±2 depending on PCM and component dimensions
Unit		see details page 153.						

▲ When ordering please specify dimension H and required packaging type.

Dims in mm.

• Diameter of pins see General Data.


Please clarify customer-specific deviations with the manufacturer.

* PCM 10 and PCM 15 can be crimped to PCM 7.5.


Position of components according to PCM 7.5 (sketch 1). P₀ = 12.7 or 15.0 is possible

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


■ ROLL Packaging



■ AMMO Packaging



■ REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumeric Bar Code

- WIMA supplier number
- Date code
- Customer's P/O number
- P/O line
- Customer's part number
- WIMA part number
- Quantity
- WIMA confirmation number
- Country of origin
- Customer name
- Handling unit number
- Week of delivery.

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- technical note
- capacitance tolerance
- packing
- connecting information

BARCODE PDF417

BARCODE 2D Datamatrix

WIMA Best Capacitors Made in Germany	
Werk Aurich	
Supplier-ID: LIEF.NR.	Date Code: 20210419
	
Purchase Order No. (P/O): Bestellung xyz	P/O line: 100
	
Customer Part No.: KUNDENTEILENUMMER	
	
WIMA Part No.: MKP1F041006B00KSSD	Quantity: 459
	
WIMA Confirmation No.: 0001105072000100	
	
Customer No.: 0000100002	RoHS 2011/65/EU
Gross Weight [g]: 4557	COO: DE
	
WIMA - MKP 10 WIMA Part No.: MKP1F041006B00KSSD	
MKP 10 1.0 µF 250 VDC 11x21x31.5 RM27.5	
Standard 10% Lose - Standard Drähte 6-2	
Vorlage Debitor Inland	
	0001105072000100
1002021443	QTY: 459 Week 19/2021

Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 27.5 mm



PCM	Size				bulk	ROLL		pcs. per packing unit				AMMO			
								REEL							
	W	H	L	Codes		H16.5	H18.5	Ø 360	Ø 500	H16.5	H18.5	340 x 340	490 x 370	H16.5	H18.5
					S	N	O	F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	0B	5000	2200		2500		–		2800		–	
	3	7.5	4.6	0C	5000	2000		2300		–		2300		–	
	3.8	8.5	4.6	0D	5000	1500		1800		–		1800		–	
	4.6	9	4.6	0E	5000	1200		1500		–		1500		–	
	5.5	10	4.6	0F	5000	900		1200		–		1200		–	
5 mm	2.5	6.5	7.2	1A	5000	2200		2500		–		2800		–	
	3	7.5	7.2	1B	5000	2000		2300		–		2300		–	
	3.5	8.5	7.2	1C	5000	1600		2000		–		2000		–	
	4.5	6	7.2	1D	6000	1300		1500		–		1500		–	
	4.5	9.5	7.2	1E	4000	1300		1500		–		1500		–	
	5	10	7.2	1F	3500	1100		1400		–		1400		–	
	5.5	7	7.2	1G	4000	1000		1200		–		1200		–	
	5.5	11.5	7.2	1H	2500	1000		1200		–		1200		–	
	6.5	8	7.2	1I	2500	800		1000		–		1000		–	
	7.2	8.5	7.2	1J	2500	700		1000		–		1000		–	
	7.2	13	7.2	1K	2000	700		950		–		1000		–	
	8.5	10	7.2	1L	2000	600		800		–		800		–	
	8.5	14	7.2	1M	1500	600		800		–		800		–	
	11	16	7.2	1N	1000	500		600		–		640		–	
7.5 mm	2.5	7	10	2A	5000	–		2500		4400		2500		–	
	3	8.5	10	2B	5000	–		2200		4300		2300		4150	
	4	9	10	2C	4000	–		1700		3200		1700		3000	
	4.5	9.5	10.3	2D	3500	–		1500		2900		1400		2700	
	5	10.5	10.3	2E	3000	–		1300		2500		1300		–	
	5.7	12.5	10.3	2F	2000	–		1000		2200		1100		–	
	7.2	12.5	10.3	2G	1500	–		900		1800		1000		–	
10 mm	3	9	13	3A	3000	–		1100		2200		–		1900	
	4	9	13	3C	3000	–		900		1600		–		1450	
	4	9.5	13	3D	3000	–		900		1600		–		1400	
	5	11	13	3F	3000	–		700		1300		–		1100	
	6	12	13	3G	2400	–		550		1100		–		1000	
	6	12.5	13	3H	2400	–		550		1100		–		1000	
	8	12	13	3I	2000	–		400		800		–		740	
15 mm	5	11	18	4B	2400	–		600		1200		–		1150	
	6	12.5	18	4C	2000	–		500		1000		–		1000	
	7	14	18	4D	1600	–		450		900		–		850	
	8	15	18	4F	1200	–		400		800		–		740	
	9	14	18	4H	1200	–		350		700		–		650	
	9	16	18	4J	900	–		350		700		–		650	
	11	14	18	4M	1000	–		300		600		–		540	
22.5 mm	5	14	26.5	5A	1200	–		–		800		–		770	
	6	15	26.5	5B	1000	–		–		700		–		640	
	7	16.5	26.5	5D	760	–		–		600		–		550	
	8.5	18.5	26.5	5F	500	–		–		480		–		450	
	10.5	19	26.5	5G	594*	–		–		400		–		360	
	10.5	20.5	26.5	5H	594*	–		–		400		–		360	
	11	21	26.5	5I	561*	–		–		380		–		350	
27.5 mm	9	19	31.5	6A	567*	–		–		460/340*		–		–	
	11	21	31.5	6B	459*	–		–		380/280*		–		–	
	13	24	31.5	6D	378*	–		–		300		–		–	
	15	26	31.5	6F	324*	–		–		270		–		–	
	17	29	31.5	6G	198*	–		–		–		–		–	
	17	34.5	31.5	6I	198*	–		–		–		–		–	
	20	39.5	31.5	6J	162*	–		–		–		–		–	

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

Rights reserved to amend design data without prior notification.



Packing Quantities for Capacitors with Radial Pins in PCM 37.5 mm to 52.5 mm

PCM	Size				bulk	ROLL		REEL				AMMO			
						H16.5	H18.5	Ø 360		Ø 500		340 x 340		490 x 370	
	W	H	L	Codes				H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5
					S	N	O	F	I	H	J	A	C	B	D
37.5 mm**	9	19	41.5	7A	441*	—	—	—	—	—	—	—	—	—	—
	11	22	41.5	7B	357*	—	—	—	—	—	—	—	—	—	—
	13	24	41.5	7C	294*	—	—	—	—	—	—	—	—	—	—
	15	26	41.5	7D	252*	—	—	—	—	—	—	—	—	—	—
	17	29	41.5	7E	154*	—	—	—	—	—	—	—	—	—	—
	19	32	41.5	7F	140*	—	—	—	—	—	—	—	—	—	—
	20	39.5	41.5	7G	126*	—	—	—	—	—	—	—	—	—	—
	24	45.5	41.5	7H	112*	—	—	—	—	—	—	—	—	—	—
	28	38	41.5	7L	84*	—	—	—	—	—	—	—	—	—	—
	31	46	41.5	7I	84*	—	—	—	—	—	—	—	—	—	—
	35	50	41.5	7J	35*	—	—	—	—	—	—	—	—	—	—
	40	55	41.5	7K	28*	—	—	—	—	—	—	—	—	—	—
48.5 mm**	19	31	56	8D	120*	—	—	—	—	—	—	—	—	—	—
	23	34	56	8E	80*	—	—	—	—	—	—	—	—	—	—
	27	37.5	56	8H	84*	—	—	—	—	—	—	—	—	—	—
	33	48	56	8J	25*	—	—	—	—	—	—	—	—	—	—
	37	54	56	8L	25*	—	—	—	—	—	—	—	—	—	—
52.5 mm	25	45	57	9D	70*	—	—	—	—	—	—	—	—	—	—
	30	45	57	9E	60*	—	—	—	—	—	—	—	—	—	—
	35	50	57	9F	25*	—	—	—	—	—	—	—	—	—	—
	45	55	57	9H	20*	—	—	—	—	—	—	—	—	—	—
	45	65	57	9J	20*	—	—	—	—	—	—	—	—	—	—

* TPS (Tray-Packing-System). Plate versions may have different packing units.

**For Snubber capacitors in 2-pin version the PCM is changing to 38.5 respective 49.5 mm.
Samples and pre-production needs on request.

Rights reserved to amend design data without prior notification.

Updated data on www.wima.com



A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	
M	K	S	2	C	0	2	1	0	0	1	A	0	0	M	S	S	D	
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2			-		20%	bulk	6 -2		
Type description:				Rated voltage:		Capacitance:			Size:					Tolerance:				
SMD-PET = SMDT				50 VDC = B0		22 pF = 0022			4.8x3.3x3 Size 1812 = KA					±20% = M				
SMD-PPS = SMDI				63 VDC = C0		47 pF = 0047			4.8x3.3x4 Size 1812 = KB					±10% = K				
FKP 02 = FKP0				100 VDC = D0		100 pF = 0100			5.7x5.1x3.5 Size 2220 = QA					±5% = J				
MKS 02 = MKS0				250 VDC = F0		150 pF = 0150			5.7x5.1x4.5 Size 2220 = QB					±2.5% = H				
FKS 2 = FKS2				400 VDC = G0		220 pF = 0220			7.2x6.1x3 Size 2824 = TA					±1% = E				
FKP 2 = FKP2				450 VDC = H0		330 pF = 0330			7.2x6.1x5 Size 2824 = TB					...				
FKS 3 = FKS3				520 VDC = H2		470 pF = 0470			10.2x7.6x5 Size 4030 = VA									
FKP 3 = FKP 3				600 VDC = I0		680 pF = 0680			12.7x10.2x6 Size 5040 = XA									
MKS 2 = MKS2				630 VDC = J0		1000 pF = 1100			15.3x13.7x7 Size 6054 = YA									
MKP 2 = MKP2				700 VDC = K0		1500 pF = 1150			2.5x7x4.6 PCM2.5 = 0B					Packing:				
MKS 4 = MKS4				800 VDC = L0		2200 pF = 1220			3x7.5x4.6 PCM2.5 = 0C					AMMO H16.5 340x340 = A				
MKP 4 = MKP4				850 VDC = M0		3300 pF = 1330			2.5x6.5x7.2 PCM5 = 1A					AMMO H16.5 490x370 = B				
MKP 10 = MKP1				900 VDC = N0		4700 pF = 1470			2.5x6.5x7.2 PCM5 = 1B					AMMO H18.5 340x340 = C				
FKP 4 = FKP4				1000 VDC = O1		6800 pF = 1680			3x7.5x7.2 PCM5 = 1B					AMMO H18.5 490x370 = D				
FKP 1 = FKP1				1100 VDC = P0		0.01 µF = 2100			2.5x7x10 PCM7.5 = 2A					REEL H16.5 360 = F				
MKP-X2 = MKX2				1200 VDC = Q0		0.01 µF = 2100			3x8.5x10 PCM7.5 = 2B					REEL H16.5 500 = H				
MKP-X1 R = MKX1				1250 VDC = R0		0.022 µF = 2220			3x9x13 PCM10 = 3A					REEL H18.5 360 = I				
MKP-Y2 = MKY2				1500 VDC = S0		0.047 µF = 2470			4x9x13 PCM10 = 3C					REEL H18.5 500 = J				
MKP 4F = MKPF				1600 VDC = T0		0.1 µF = 3100			5x11x18 PCM15 = 4B					ROLL H16.5 = N				
Snubber MKP = SNMP				1700 VDC = TA		0.22 µF = 3220			6x12.5x18 PCM15 = 4C					ROLL H18.5 = O				
Snubber FKP = SNFP				2000 VDC = U0		0.47 µF = 3470			5x14x26.5 PCM22.5 = 5A					BLISTER W12 180 = P				
GTO MKP = GTOM				2500 VDC = V0		1 µF = 4100			6x15x26.5 PCM22.5 = 5B					BLISTER W12 330 = Q				
DC-LINK MKP 4 = DCP4				3000 VDC = W0		2.2 µF = 4220			9x19x31.5 PCM27.5 = 6A					BLISTER W16 330 = R				
DC-LINK MKP 6 = DCP6				4000 VDC = X0		4.7 µF = 4470			11x21x31.5 PCM27.5 = 6B					BLISTER W24 330 = T				
DC-LINK HC = DCHC				6000 VDC = Y0		10 µF = 5100			9x19x41.5 PCM37.5 = 7A					Bulk/TPS Standard = S				
				22 µF = 5220		22 µF = 5220			11x22x41.5 PCM37.5 = 7B					...				
				230 VAC = 3Y		47 µF = 5470			19x31x56 PCM 48.5 = 8D									
				275 VAC = 1W		100 µF = 6100			25x45x57 PCM 52.5 = 9D									
				300 VAC = 2W		220 µF = 6220			...									
				305 VAC = AW		1000 µF = 7100												
				350 VAC = BW		1500 µF = 7150												
				440 VAC = 4W		...												
				...														
							Version code:						Pin length (untaped)					
							Standard = 00						3.5 ±0.5 = C9					
							Version A1 = 1A						6 -2 = SD					
							Version A1.1.1 = 1B						16 ±1 = P1					
							Version A2 = 2A						...			Pin length (taped)		
							...									none = 00		

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.