



Part Number : [313872034](#)

Product Description : 2.54mm Pitch, MX123 Header, 73 Circuits Shrouded Assembly, Qty(72) 0.64mm Square Signal Pins + Qty(1) 2.8mm Power Blade, Harness Side Key Code A, Black (Ag Mate Side Finish)

Series Number : 31387

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[313872034 sd.pdf](#)

[PK-31301-916-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[AS-31386-200-001.pdf](#)

[PS-31387-200-001.pdf](#)

[TS-31387-1658-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	PCB Headers and Receptacles
Series	31387
Description	2.54mm Pitch, MX123 Header, 73 Circuits Shrouded Assembly, Qty(72) 0.64mm Square Signal Pins + Qty(1) 2.8mm Power Blade, Harness Side Key Code A, Black (Ag Mate Side Finish)
Application	Automotive, Power, Wire-to-Board
Component Type	PCB Header
Product Name	MX123
UPC	884982908864

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	73
Circuits (maximum)	73
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	23.220/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Carton
PCB Locator	No
PCB Retention	No
PC Tail Length	6.50mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

MX123 Receptacle Housings	<u>34566</u>
---------------------------	--------------

Use with Part(s)

Description	Part Number
MX64 Female Terminals	<u>34736</u>

This document was generated on Apr 23, 2026