

IRFN9140 (JANTX2N7236U)

PD-91553G

Power MOSFET

Surface Mount (SMD-1)

-100V, -18A, P-channel, HEXFET™ MOSFET Technology

Features

- Simple drive requirements
- Hermetically sealed
- Electrically isolated
- Surface mount
- Dynamic dv/dt rating
- Light Weight

Product Summary

- BV_{DSS} : -100V
- I_D : -18A
- $R_{DS(on),max}$: 0.20Ω
- $Q_{G,max}$: 60nC
- **REF**: MIL-PRF-19500/595

Potential Applications

- DC-DC converter
- Motor drives



Product Validation

Qualified to JANTXV screening flow according to MIL-PRF-19500 for high-reliability applications

Description

HEXFET MOSFET technology is the key to IR HiRel advanced line of power MOSFET transistors. The efficient geometry design achieves very low on-state resistance combined with high transconductance. HEXFET transistors also feature all of the well-established advantages of MOSFETs, such as voltage control, very fast switching and electrical parameter temperature stability. They are well-suited for applications such as switching power supplies, motor controls, inverters, choppers, audio amplifiers, high energy pulse circuits, and virtually any application where high reliability is required. The HEXFET transistor's totally isolated package eliminates the need for additional isolating material between the device and the heat sink. This improves thermal efficiency and reduces drain capacitance.

Ordering Information

Table 1 Ordering options

| Part number | Package | Screening Level |
|---------------|---------|-----------------|
| IRFN9140 | SMD-1 | COTS |
| JANTX2N7236U | SMD-1 | JANTX |
| JANTXV2N7236U | SMD-1 | JANTXV |

Table of contents**Table of contents**

| | |
|--|-----------|
| Features | 1 |
| Potential Applications..... | 1 |
| Product Validation..... | 1 |
| Description | 1 |
| Table of contents..... | 2 |
| 1 Absolute Maximum Ratings | 3 |
| 2 Device Characteristics | 4 |
| 2.1 Electrical Characteristics | 4 |
| 2.2 Source-Drain Diode Ratings and Characteristics | 5 |
| 2.3 Thermal Characteristics | 5 |
| 3 Electrical Characteristics Curves..... | 6 |
| 4 Test Circuits | 9 |
| 5 Package Outline | 10 |
| Revision history..... | 11 |

Absolute Maximum Ratings**1 Absolute Maximum Ratings****Table 2 Absolute Maximum Ratings**

| Symbol | Parameter | Value | Unit |
|--|---|---------------|------|
| I_{D1} @ $V_{GS} = -10V$, $T_c = 25^\circ C$ | Continuous Drain Current | -18 | A |
| I_{D2} @ $V_{GS} = -10V$, $T_c = 100^\circ C$ | Continuous Drain Current | -11 | A |
| I_{DM} @ $T_c = 25^\circ C$ | Pulsed Drain Current ¹ | -72 | A |
| P_D @ $T_c = 25^\circ C$ | Maximum Power Dissipation | 125 | W |
| | Linear Derating Factor | 1.0 | W/°C |
| V_{GS} | Gate-to-Source Voltage | ± 20 | V |
| E_{AS} | Single Pulse Avalanche Energy ² | 500 | mJ |
| I_{AR} | Avalanche Current ¹ | -18 | A |
| E_{AR} | Repetitive Avalanche Energy ¹ | 12.5 | mJ |
| dv/dt | Peak Diode Reverse Recovery ³ | -5.0 | V/ns |
| T_J T_{STG} | Operating Junction and Storage Temperature Range | -55 to +150 | °C |
| | Lead Temperature | 300 (for 5 s) | |
| | Weight | 2.6 (Typical) | g |

¹ Repetitive Rating; Pulse width limited by maximum junction temperature.² $V_{DD} = -25V$, starting $T_J = 25^\circ C$, $L = 3.1mH$, Peak $I_L = -18A$, $V_{GS} = -10V$ ³ $I_{SD} \leq -18A$, $di/dt \leq -100A/\mu s$, $V_{DD} \leq -100V$, $T_J \leq 150^\circ C$

Device Characteristics

2 Device Characteristics

2.1 Electrical Characteristics

Table 3 Static and Dynamic Electrical Characteristics @ $T_j = 25^\circ\text{C}$ (Unless Otherwise Specified)

| Symbol | Parameter | Min. | Typ. | Max. | Unit | Test Conditions |
|------------------------------|--|------|--------|------|---------------------|--|
| BV_{DSS} | Drain-to-Source Breakdown Voltage | -100 | — | — | V | $V_{GS} = 0\text{V}$, $I_D = -1.0\text{mA}$ |
| $\Delta BV_{DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient | — | -0.087 | — | V/ $^\circ\text{C}$ | Reference to 25°C , $I_D = -1.0\text{mA}$ |
| $R_{DS(on)}$ | Static Drain-to-Source On-State Resistance | — | — | 0.20 | Ω | $V_{GS} = -10\text{V}$, $I_{D2} = -11\text{A}^1$ |
| | | — | — | 0.22 | | $V_{GS} = -10\text{V}$, $I_{D2} = -18\text{A}^1$ |
| $V_{GS(th)}$ | Gate Threshold Voltage | -2.0 | — | -4.0 | V | $V_{DS} = V_{GS}$, $I_D = -250\mu\text{A}$ |
| G_{fs} | Forward Transconductance | 6.2 | — | — | S | $V_{DS} = -15\text{V}$, $I_{D2} = -11\text{A}^1$ |
| I_{DSS} | Zero Gate Voltage Drain Current | — | — | -25 | μA | $V_{DS} = -80\text{V}$, $V_{GS} = 0\text{V}$ |
| | | — | — | -250 | | $V_{DS} = -80\text{V}$, $V_{GS} = 0\text{V}$, $T_J = 125^\circ\text{C}$ |
| I_{GSS} | Gate-to-Source Leakage Forward | — | — | -100 | nA | $V_{GS} = -20\text{V}$ |
| | Gate-to-Source Leakage Reverse | — | — | 100 | | $V_{GS} = 20\text{V}$ |
| Q_G | Total Gate Charge | — | — | 60 | nC | $I_{D1} = -18\text{A}$ $V_{DS} = -50\text{V}$ $V_{GS} = -10\text{V}$ |
| Q_{GS} | Gate-to-Source Charge | — | — | 13 | | |
| Q_{GD} | Gate-to-Drain ('Miller') Charge | — | — | 35.2 | | |
| $t_{d(on)}$ | Turn-On Delay Time | — | — | 35 | | |
| t_r | Rise Time | — | — | 85 | ns | $I_{D1} = -18\text{A}^{**}$ $V_{DD} = -50\text{V}$ $R_G = 9.1\Omega$ $V_{GS} = -10\text{V}$ |
| $t_{d(off)}$ | Turn-Off Delay Time | — | — | 85 | | |
| t_f | Fall Time | — | — | 65 | | |
| $L_s + L_D$ | Total Inductance | — | 4.0 | — | nH | Measured from the center of drain pad to center of source pad |
| C_{iss} | Input Capacitance | — | 1400 | — | pF | $V_{GS} = 0\text{V}$ |
| C_{oss} | Output Capacitance | — | 600 | — | | $V_{DS} = -25\text{V}$ |
| C_{rss} | Reverse Transfer Capacitance | — | 200 | — | | $f = 1.0\text{MHz}$ |

** Switching speed maximum limits are based on manufacturing test equipment and capability.

¹ Pulse width $\leq 300\ \mu\text{s}$; Duty Cycle $\leq 2\%$

Device Characteristics

2.2 Source-Drain Diode Ratings and Characteristics

Table 4 Source-Drain Diode Characteristics

| Symbol | Parameter | Min. | Typ. | Max. | Unit | Test Conditions |
|----------|---|---|------|------|---------------|---|
| I_S | Continuous Source Current (Body Diode) | — | — | -18 | A | |
| I_{SM} | Pulsed Source Current (Body Diode) ¹ | — | — | -72 | A | |
| V_{SD} | Diode Forward Voltage | — | — | -5.0 | V | $T_J = 25^\circ\text{C}$, $I_S = -18\text{A}$, $V_{GS} = 0\text{V}$ ² |
| t_{rr} | Reverse Recovery Time | — | — | 280 | ns | $T_J = 25^\circ\text{C}$, $I_F = -18\text{A}$, $V_{DD} \leq -30\text{V}$ $di/dt = -100\text{A}/\mu\text{s}$ ² |
| Q_{rr} | Reverse Recovery Charge | — | 2.4 | — | μC | |
| t_{on} | Forward Turn-On Time | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$) | | | | |

2.3 Thermal Characteristics

Table 5 Thermal Resistance

| Symbol | Parameter | Min. | Typ. | Max. | Unit |
|--------------------|---|------|------|------|---------------------------|
| $R_{\theta JC}$ | Junction-to-Case | — | — | 1.0 | $^\circ\text{C}/\text{W}$ |
| $R_{\theta J-PCB}$ | Junction-to-PC Board (Soldered to a copper-clad PC board) | — | 4.0 | — | |

¹ Repetitive Rating; Pulse width limited by maximum junction temperature.² Pulse width $\leq 300\ \mu\text{s}$; Duty Cycle $\leq 2\%$

Electrical Characteristics Curves

3 Electrical Characteristics Curves




Figure 1 Typical Output Characteristics

Figure 2 Typical Output Characteristics




Figure 3 Typical Transfer Characteristics

Figure 4 Normalized On-Resistance Vs. Temperature

Electrical Characteristics Curves




Figure 5 Typical Capacitance Vs.
Drain-to-Source Voltage

Figure 6 Typical Gate Charge Vs.
Gate-to-Source Voltage




Figure 7 Typical Source-Drain Diode Forward
Voltage

Figure 8 Maximum Safe Operating Area

Electrical Characteristics Curves




Figure 9 Maximum Drain Current Vs.
Case Temperature




Figure 10 Maximum Avalanche Energy Vs.
Junction Temperature




Figure 11 Maximum Effective Transient Thermal Impedance, Junction-to-Case

Test Circuits

4 Test Circuits




Figure 12 Gate Charge Test Circuit




Figure 13 Gate Charge Waveform




Figure 14 Unclamped Inductive Test Circuit




Figure 15 Unclamped Inductive Waveform




Figure 16 Switching Time Test Circuit





Figure 17 Switching Time Waveforms

Package Outline

5 Package Outline

Note: For the most updated package outline, please see the website: [SMD-1](#)



Revision history

| Document version | Date of release | Description of changes |
|-------------------------|------------------------|--|
| Rev | 12/22/1999 | Datasheet (PD-91553C) |
| Rev D | 02/05/2002 | ADDED Slash sheet # 595 -page1 |
| Rev E | 01/29/2002 | Added Swichting test condition $V_{GS}=-10V$ |
| Rev F | 09/22/2003 | Updated based on ECN-11069 |
| Rev G | 12/06/2024 | Updated based on ECN-1120_10102 |

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-12-06

Published by

**International Rectifier HiRel Products,
Inc.**

**An Infineon Technologies company
El Segundo, California 90245 USA**

**© 2024 Infineon Technologies AG.
All Rights Reserved.**

**Do you have a question about this
document?**

Email: erratum@infineon.com

Document reference

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., an Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.