





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/29/16	
A		UPDATE DIM.	7/17/18	AY/RT



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
 Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
 Insulator color: Black
 Contacts: Phosphor Bronze
 Plating:
 Gold flash over Nickel underplate overall
 Electrical:
 Current rating: 0.75 Amp
 Contact resistance: 20 mohms max
 Insulation resistance: 1,000 Mohms min.
 Dielectric withstanding voltage: 500 VAC
 Temperature Rating:
 -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



Positions: 04 thru 100

A= .031 [0.80] x No. of Positions per row + .008 [0.20]

B= .031 [0.80] x No. of Spaces per row

C= .031 [0.80] x No. of Positions per row - .063 [1.60]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		TITLE					
DRAWN		HR		4/29/16		.031 [0.80] X .047 [1.20] FEMALE HEADER, SMT, DUAL ROW, GOLD PLATED, .122 [3.10] HEIGHT	
CHECKED		CH		4/29/16		SIZE X	
APPROVED						PART NO. SRS2Y-XX-U-SMT	
						REV. A	
				REF: S00111C		SCALE: NTS	
						SHEET 1 OF 1	