

Part Number : 1300545003
Product Description : Ultra-Lock (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Female (Straight) to RJ-45 Male (Straight), 24 AWG, PVC Cable, 1.0m (3.28') Length
Series Number : 130054
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : ERWPAU7003M010

Documents and Resources

Drawings

1300545003_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active SCIP:Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Obsolete

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	130054
Description	Ultra-Lock (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Female (Straight) to RJ-45 Male (Straight), 24 AWG, PVC Cable, 1.0m (3.28') Length
IP Rating	IP20, IP67 (M12 only)
Performance Category	5e
Product Name	Industrial Ethernet,Ultra-Lock (M12),RJ45
Protocol	EtherNet
Type	Double Ended
UPC	883906399139

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	150V AC

Physical

Cable Diameter	N/A
Cable Length	1.0m (3.28')
Color - Cable Jacket	Teal
Connector End A	Ultra-Lock (M12)
Connector End B	RJ-45 (industrial)
Coupling Style	Push and Latch, Push to Lock
Gender	Female-Male
Keyway	D-Coded

Obsolete

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	156.600/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +75°C
Wire/Cable Type	E152210
Wire Size (AWG)	24

Obsolete

Downloaded from Arrow.com.