

PFT male rear L-coded 2.5mm² w/o FE



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 599 1516
Specification	PFT male rear L-coded 2.5mm ² w/o FE
HARTING eCatalogue	https://b2b.harting.com/21035991516

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	Panel feed through
Specification	With conductors for rear mounting

Version

Gender	Male
Shielding	Unshielded
Number of contacts	4
Coding	L-coding
Locking type	Screw locking

Technical characteristics

Conductor cross-section	2.5 mm ²
Conductor cross-section	AWG 14
Rated current	16 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	>10 ⁸ Ω



Pushing Performance
Since 1945

Technical characteristics

Contact resistance	≤10 mΩ
Tightening torque	2 Nm Lock nut
Wrench size	17
	18
Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I (600 ≤ CTI)
Conductor length	30 cm

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-111
UL / CSA	UL 2238 CYJV2.E302521
	CSA-C22.2 No. 182.3 CYJV8.E302521
PROFINET	Yes



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	48.9 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140227613
eCl@ss	27440103 Sensor-actuator connector chassis (sensor technology acc.)