

200mW, Dual PNP Small Signal Transistor

FEATURES

- AEC-Q101 qualified
- General-purpose transistors
- Ideal for automated placement
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free

APPLICATIONS




- General switching and amplification

MECHANICAL DATA

- Case: SOT-363
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Weight: 6.99mg (approximately)



KEY PARAMETERS		
PARAMETER	VALUE	UNIT
V_{CBO}	-80	V
V_{CEO}	-65	V
V_{EBO}	-5	V
I_C	-100	mA
h_{FE}	450	
Configuration	Dual die	

PACKAGE: SOT-363	PIN CONFIGURATION	CIRCUIT DIAGRAM
		

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Power dissipation ⁽¹⁾	P_D	200	mW
Collector-base voltage	V_{CBO}	-80	V
Collector-emitter voltage	V_{CEO}	-65	V
Emitter-base voltage	V_{EBO}	-5	V
Collector current	I_C	-100	mA
Junction temperature	T_J	-55 to +150	$^\circ\text{C}$
Storage temperature	T_{STG}	-55 to +150	$^\circ\text{C}$

Note:

1. Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-ambient thermal resistance ⁽¹⁾	$R_{\theta JA}$	625	°C/W

Thermal Performance Note:

- Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$I_C = -10\mu\text{A}$, $I_E = 0\text{A}$	$V_{(BR)CBO}$	-80	-	-	V
Collector-emitter breakdown voltage	$I_C = -10\text{mA}$, $I_B = 0\text{A}$	$V_{(BR)CEO}$	-65	-	-	V
Emitter-base breakdown voltage	$I_E = -10\mu\text{A}$, $I_C = 0\text{A}$	$V_{(BR)EBO}$	-5	-	-	V
Collector-base cut-off current	$V_{CB} = -30\text{V}$, $I_E = 0\text{A}$	I_{CBO}	-	-	-15	nA
Emitter-base cut-off current	$V_{EB} = -5\text{V}$, $I_C = 0\text{A}$	I_{EBO}	-	-	-0.1	μA
DC current gain	$V_{CE} = -5\text{V}$, $I_C = -2\text{mA}$	h_{FE}	200	-	450	-
Collector-emitter saturation voltage	$I_C = -10\text{mA}$, $I_B = -0.5\text{mA}$	$V_{CE(sat)}$	-	-	-0.1	V
	$I_C = -100\text{mA}$, $I_B = -5\text{mA}$		-	-	-0.3	
Base-emitter saturation voltage	$I_C = -10\text{mA}$, $I_B = -0.5\text{mA}$	$V_{BE(sat)}$	-	-750	-850	mV
Base-emitter voltage	$V_{CE} = -5\text{V}$, $I_C = -2\text{mA}$	V_{BE}	-	-	-750	mV
Transition frequency	$V_{CE} = -5\text{V}$, $I_C = -10\text{mA}$, $f = 100\text{MHz}$	f_T	100	-	-	MHz
Output capacitance	$V_{CB} = -10\text{V}$, $I_E = 0\text{A}$, $f = 1\text{MHz}$	C_{obo}	-	-	4.5	pF

ORDERING AND MARKING INFORMATION

ORDERING CODE	PACKAGE	PACKING
BC856BSH RFG	SOT-363	3,000 / 7" Tape & Reel

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Power Dissipation Curve




Fig.2 Typical Capacitance Characteristics




Fig.3 DC Current Gain vs. Collector Current




Fig.4 Collector-Emitter Saturation Voltage vs. Collector Current




Fig.5 Base-Emitter Saturation Voltage vs. Collector Current






Fig.6 Base-Emitter Voltage vs. Collector Current



PACKAGE OUTLINE DIMENSIONS

SOT-363




MARKING DIAGRAM

5Ft = Device marking
 F = Factory code
 Y = Year code
 W = Bi-Week code (A~Z)

NOTES: UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS ARE IN MILLIMETERS.
- DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- PACKAGE OUTLINE REFERENCE: JEITA ED-7500A, EIAJ SC-88.
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
- DWG NO. REF: HQ2SD07-SOT363-097 REV B.



SUGGESTED PAD LAYOUT

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.