





PRODUCT NUMBER	PITCH
T7xx23x000J0G	9.52 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item (a) Terminal housing : Thermoplastic (UL 94V-0)
- Item (b) Clamp: Brass ,Ni plated
- Item (c) Solder pin: Copper, Tin plated
- Item (d) Terminal screw: Steel Zinc plating"- "slot type

- Electrical cULus TUV
- Voltage rating: 300VAC 750VAC
 - Current rating: 30A 41A
 - Wire range: 0.20-6.0mm²
 - Solid wire(AWG): 10-24
 - Stranded wire(AWG): 10-24
 - Torque: 6.9 Lb-in 0.85 N.m
 - Screw: M3.5
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV 3.0KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval:

PART NO.: T7 xx 2 3 x 0 00J0 G

N = Number of poles
Dim L=Nx9.52
Dim B=(N-1)x9.52

Poles	Tolerance
2-6p	±0.20
7-11p	±0.30
12-16p	±0.40

End Stackable	No. of poles	Body Color	RoHS compliant
0	2	Black (RAL9005)	(lead<4%)
02	2 poles	Red (RAL3001/D)	In copper Alloy
03	3 poles	Orange(RAL2011/P)	
4	4 poles	Yellow(RAL1018/A)	
5	5 poles	Green(RAL6018/T)	
6	6 poles	Blue (RAL5015/A)	
8	8 poles	Grey(RAL7035/D)	
9	9 poles	White(RAL1102)	
C	16 poles	Green(RAL6018/U)	

mat'l. code		surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date		title TERMINAL BLOCK
				tolerances unless otherwise specified	scale RISING CLAMP,180D WIRE INLET,END STACKABLE
				angles X°±1°	scale MM
				dr	dwg no
				enr	sheet 1 of 1 size
				chr	T7xx23x000J0G A4
				appd	type CUSTOMER Drawing
sheet index	revision sheet	A	1		