







Color: ■ light gray



This analog input module processes standard 4–20 mA signals.  
The input signal is electrically isolated and is transmitted with a resolution of 12 bits.  
The internal system supply powers the module.  
The input channels of the module have a common ground potential.

| Technical data                                                 |                                                                                                                                                      |
|----------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Number of analog inputs                                        | 4                                                                                                                                                    |
| Total number of channels (module)                              | 4                                                                                                                                                    |
| Signal type                                                    | Current                                                                                                                                              |
| Signal type (current)                                          | 4 ... 20 mADC                                                                                                                                        |
| Sensor connection                                              | 4 x (2-wire)                                                                                                                                         |
| Input voltage (max.)                                           | 32 V                                                                                                                                                 |
| Signal characteristics                                         | Single-ended                                                                                                                                         |
| Resolution [bit]                                               | 12 bits                                                                                                                                              |
| Input resistance (max.)                                        | 100 Ω                                                                                                                                                |
| Data width                                                     | 4 x 16-bit data; 4 x 8-bit control/status (optional)                                                                                                 |
| Conversion time (typ.)                                         | 10 ms                                                                                                                                                |
| Measurement error (reference temperature)                      | 25 °C                                                                                                                                                |
| Measurement error, deviation (max.) from the upper-range value | 0.1 %                                                                                                                                                |
| Temperature error (max.) of the upper-range value              | 0.01 %/K                                                                                                                                             |
| Supply voltage (system)                                        | 5 VDC; via data contacts                                                                                                                             |
| Current consumption (5 V system supply)                        | 65 mA                                                                                                                                                |
| Supply voltage (field)                                         | 24 VDC (-25 ... +30 %); via power jumper contacts (power supply via blade contact; transmission (field side supply voltage only) via spring contact) |
| Isolation                                                      | 500 V system/field                                                                                                                                   |



| Technical data                           |  |                                    |
|------------------------------------------|--|------------------------------------|
| Indicators                               |  | LED (A-D) red: Error AI 1 ... AI 4 |
| Number of incoming power jumper contacts |  | 2                                  |
| Number of outgoing power jumper contacts |  | 2                                  |

| Connection data                       |  |                                   |
|---------------------------------------|--|-----------------------------------|
| Connection technology: inputs/outputs |  | 8 x CAGE CLAMP®                   |
| Connectable conductor materials       |  | Copper                            |
| Connection type 1                     |  | Inputs/outputs                    |
| Solid conductor                       |  | 0.08 ... 2.5 mm² / 28 ... 14 AWG  |
| Fine-stranded conductor               |  | 0.08 ... 2.5 mm² / 28 ... 14 AWG  |
| Strip length                          |  | 8 ... 9 mm / 0.31 ... 0.35 inches |

| Physical data                     |  |                        |
|-----------------------------------|--|------------------------|
| Width                             |  | 12 mm / 0.472 inches   |
| Height                            |  | 100 mm / 3.937 inches  |
| Depth                             |  | 69.8 mm / 2.748 inches |
| Depth from upper-edge of DIN-rail |  | 62.6 mm / 2.465 inches |

| Mechanical data     |  |             |
|---------------------|--|-------------|
| Mounting type       |  | DIN-35 rail |
| Pluggable connector |  | fixed       |

| Material data      |  |                              |
|--------------------|--|------------------------------|
| Color              |  | light gray                   |
| Housing material   |  | Polycarbonate; polyamide 6.6 |
| Fire load          |  | 1.286 MJ                     |
| Weight             |  | 52 g                         |
| Conformity marking |  | CE                           |

| Environmental requirements                                                         |  |                                                                                                        |
|------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                                                    |  | 0 ... +55 °C                                                                                           |
| Ambient temperature (storage)                                                      |  | -40 ... +85 °C                                                                                         |
| Protection type                                                                    |  | IP20                                                                                                   |
| Pollution degree                                                                   |  | 2 per IEC 61131-2                                                                                      |
| Operating altitude                                                                 |  | 0 ... 2000 m / 0 ... 6562 ft                                                                           |
| Mounting position                                                                  |  | Horizontal left, horizontal right, horizontal top, horizontal bottom, vertical top and vertical bottom |
| Relative humidity (without condensation)                                           |  | 95 %                                                                                                   |
| Vibration resistance                                                               |  | 4g per IEC 60068-2-6                                                                                   |
| Shock resistance                                                                   |  | 15g per IEC 60068-2-27                                                                                 |
| EMC immunity to interference                                                       |  | per EN 61000-6-2, marine applications                                                                  |
| EMC emission of interference                                                       |  | per EN 61000-6-4, marine applications                                                                  |
| Exposure to pollutants                                                             |  | per IEC 60068-2-42 and IEC 60068-2-43                                                                  |
| Permissible H <sub>2</sub> S contaminant concentration at a relative humidity 75 % |  | 10 ppm                                                                                                 |
| Permissible SO <sub>2</sub> contaminant concentration at a relative humidity 75 %  |  | 25 ppm                                                                                                 |



| Commercial data       |                 |
|-----------------------|-----------------|
| Product Group         | 15 (I/O System) |
| PU (SPU)              | 1 pcs           |
| Packaging type        | Box             |
| Country of origin     | DE              |
| GTIN                  | 4045454439606   |
| Customs tariff number | 85389099990     |

| Product classification |          |
|------------------------|----------|
| UNSPSC                 | 32101502 |

| Environmental Product Compliance          |                                           |
|-------------------------------------------|-------------------------------------------|
| CAS-No.                                   | 1303-86-2<br>1317-36-8<br>7439-92-1       |
| REACH Candidate List Substance            | Diboron trioxide<br>Lead<br>Lead monoxide |
| RoHS Compliance Status                    | Compliant,With Exemption                  |
| RoHS Exemption                            | 6(c)<br>7(a)<br>7(c)-I<br>7(c)-II         |
| SCIP notification number (Austria)        | 236d4246-1547-46ff-aa98-585795c2ea72      |
| SCIP notification number (Belgium)        | 188731cf-f22c-4900-9119-a9616d6b701c      |
| SCIP notification number (Bulgaria)       | 747643ad-866b-4edc-87b5-f8e92cb74b17      |
| SCIP notification number (Czech Republic) | 32631e7c-0884-436b-8e84-7a6a6585dbd9      |
| SCIP notification number (Denmark)        | 64209a78-edac-4fd1-899b-8af15a73700d      |
| SCIP notification number (Finland)        | aae38999-f9c8-4449-a196-5068e6236a60      |
| SCIP notification number (France)         | acff81c7-e82f-4344-8f65-66f4aa359a9b      |
| SCIP notification number (Germany)        | 40795e90-d056-4c93-ba0e-2b2792a74488      |
| SCIP notification number (Hungary)        | 053e0443-979d-421a-b23e-2d286331a9ca      |
| SCIP notification number (Italy)          | 635e992c-88e7-4dc5-833c-8be0f7c35b32      |
| SCIP notification number (Netherlands)    | d9e4c20e-ddf1-461d-ad7a-8e3facf4e359      |
| SCIP notification number (Poland)         | b23b5eea-5dab-4baa-89e1-e8bd37efbdb8      |
| SCIP notification number (Romania)        | 42ad3d9f-b0b7-44c3-a36f-8f30391def72      |
| SCIP notification number (Sweden)         | d15e461c-1a42-4b90-865d-44f88540466d      |

| Approvals / Certificates                                                           |                        |                                                                                                                                                                                                                                                                                           |          |          |                  |                                                         |   |   |                                                         |   |   |
|------------------------------------------------------------------------------------|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|----------|------------------|---------------------------------------------------------|---|---|---------------------------------------------------------|---|---|
| General approvals                                                                  |                        | Declarations of conformity and manufacturer's declarations                                                                                                                                                                                                                                |          |          |                  |                                                         |   |   |                                                         |   |   |
|  |                        |                                                                                                                                                                                                                                                                                           |          |          |                  |                                                         |   |   |                                                         |   |   |
| Approval                                                                           | Standard               | Certificate Name                                                                                                                                                                                                                                                                          |          |          |                  |                                                         |   |   |                                                         |   |   |
| EAC<br>GZO Almaty Standart                                                         | TP TC 020/2011         | EAC CoC 03083                                                                                                                                                                                                                                                                             |          |          |                  |                                                         |   |   |                                                         |   |   |
| KC<br>National Radio Research Agency                                               | Article 58-2, Clause 3 | MSIP-REM-W43-AIM750                                                                                                                                                                                                                                                                       |          |          |                  |                                                         |   |   |                                                         |   |   |
|                                                                                    |                        | <table><tr><th>Approval</th><th>Standard</th><th>Certificate Name</th></tr><tr><td>EU-Declaration of Confor-<br/>mity<br/>WAGO GmbH &amp; Co. KG</td><td>-</td><td>-</td></tr><tr><td>UK-Declaration of Confor-<br/>mity<br/>WAGO GmbH &amp; Co. KG</td><td>-</td><td>-</td></tr></table> | Approval | Standard | Certificate Name | EU-Declaration of Confor-<br>mity<br>WAGO GmbH & Co. KG | - | - | UK-Declaration of Confor-<br>mity<br>WAGO GmbH & Co. KG | - | - |
| Approval                                                                           | Standard               | Certificate Name                                                                                                                                                                                                                                                                          |          |          |                  |                                                         |   |   |                                                         |   |   |
| EU-Declaration of Confor-<br>mity<br>WAGO GmbH & Co. KG                            | -                      | -                                                                                                                                                                                                                                                                                         |          |          |                  |                                                         |   |   |                                                         |   |   |
| UK-Declaration of Confor-<br>mity<br>WAGO GmbH & Co. KG                            | -                      | -                                                                                                                                                                                                                                                                                         |          |          |                  |                                                         |   |   |                                                         |   |   |



Approvals for marine applications



| Approval                                                        | Standard             | Certificate Name  |
|-----------------------------------------------------------------|----------------------|-------------------|
| ABS<br>American Bureau of Ship-<br>ping                         | -                    | 22-2219060        |
| BSH<br>Bundesamt fuer See-<br>schifffahrt und Hydrogra-<br>phie | -                    | 1104              |
| BV<br>Bureau Veritas S.A.                                       | -                    | 13453/E0 BV       |
| DNV<br>DNV GL SE                                                | DNV-CG-0339,Aug.2021 | TAA0000194        |
| KR<br>Korean Register of Ship-<br>ping                          | -                    | KR HMB05880-AC001 |
| LR<br>Lloyds Register EMEA                                      | -                    | LR22180952TA      |
| PRS<br>Polski Rejestr Statków                                   | -                    | TE/1101/880590/23 |
| RINA<br>RINA Germany GmbH                                       | -                    | ELE343521XG001    |

Approvals for hazardous areas



| Approval                                    | Standard                        | Certificate Name                              |
|---------------------------------------------|---------------------------------|-----------------------------------------------|
| ATEX<br>TUEV Nord Cert GmbH                 | EN 60079-0                      | TUEV14ATEX148929X (II<br>3 G Ex ec IIC T4 Gc) |
| CCCEX<br>CQST/CNEx                          | CNCA-C23-01                     | 2020312310000213 (Ex<br>ec IIC T4 Gc)         |
| IECEx<br>TUEV Nord Cert GmbH                | IEC 60079-0                     | IECEx TUN 14.0035 X (Ex<br>ec IIC T4 Gc)      |
| INMETRO<br>TÜV Rheinland do Brasil<br>Ltda. | IEC 60079-0                     | TÜV 12.1297 X                                 |
| KTL<br>Korea Testing Laboratory             | KOSHA Article 34,<br>IEC60079-0 | 21-KA4BO-0550X                                |
| UKEx<br>WAGO GmbH & Co. KG                  | EN 60079-0                      | UKCA_WA<br>GO22UKEX003X_ec                    |

Downloads

Environmental Product Compliance

| Compliance Search                           |
|---------------------------------------------|
| Environmental Product<br>Compliance 750-455 |

Documentation

| Manual                                                  | System Description                                               |
|---------------------------------------------------------|------------------------------------------------------------------|
| Product Manual 4-<br>channel, 4-20mA, sin-<br>gle-ended | 750/753 Series I/O-<br>System – General Pro-<br>duct Information |
| System Manual Series<br>750/753                         | Overview on WAGO-I/<br>O-SYSTEM 750 appro-<br>vals               |

| Bid Text                   |
|----------------------------|
| 750-455                    |
| 19.02.2019                 |
| xml<br>4.17 KB             |
| 750-455                    |
| 17.10.2017                 |
| doc<br>27.50 KB            |
| 750-455                    |
| 17.10.2017                 |
| docx<br>17.06 KB           |
| ausschreiben.de<br>750-455 |

| Instruction Leaflet                  |
|--------------------------------------|
| CCC Ex (Additional in-<br>formation) |
| 26.04.2023                           |
| pdf<br>159.76 KB                     |



| CAD/CAE-Data         |                           |
|----------------------|---------------------------|
| CAD data             | CAE data                  |
| 2D/3D Models 750-455 | EPLAN Data Portal 750-455 |
|                      | WSCAD Universe 750-455    |
|                      | ZUKEN Portal 750-455      |

| Device Files                                       |                       |                   |  |
|----------------------------------------------------|-----------------------|-------------------|--|
| Device Driver                                      |                       |                   |  |
| WAGO USB Service Kabel Treiber / Serie 750 und 857 | 6.5.3.0<br>10.09.2014 | zip<br>4721.96 KB |  |

| 1 Compatible Products        |
|------------------------------|
| 1.1 Optional Accessories     |
| 1.1.1 DIN-rail               |
| 1.1.1.1 Mounting accessories |

|                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                      |                                                                                                                                                                                                                                      |                                                                                                                                                                                                                                               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <br><b>Item No.: 210-196</b><br>Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored               | <br><b>Item No.: 210-198</b><br>Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored         | <br><b>Item No.: 210-508</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; similar to EN 60715; silver-colored | <br><b>Item No.: 210-197</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored                     |
| <br><b>Item No.: 210-506</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; similar to EN 60715; silver-colored       | <br><b>Item No.: 210-114</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored            | <br><b>Item No.: 210-118</b><br>Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored         | <br><b>Item No.: 210-115</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored |
| <br><b>Item No.: 210-112</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored | <br><b>Item No.: 210-504</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715; silver-colored | <br><b>Item No.: 210-113</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored          | <br><b>Item No.: 210-505</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715; silver-colored      |

| 1.1.2 Marking                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------|
| 1.1.2.1 Group marker carrier                                                                                                            |
| <br><b>Item No.: 750-106</b><br>Group marker carrier |



1.1.2.2 Marker

|                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                      |                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                         |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <br><b>Item No.: 750-100</b><br>Marker card; as a DIN A4 sheet; plain                                                                                 | <br><b>Item No.: 2009-145/000-006</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue | <br><b>Item No.: 2009-145/000-007</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray   | <br><b>Item No.: 2009-145/000-023</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green |
| <br><b>Item No.: 2009-145/000-012</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange | <br><b>Item No.: 2009-145/000-005</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red  | <br><b>Item No.: 2009-145/000-024</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet | <br><b>Item No.: 2009-145</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white         |
| <br><b>Item No.: 2009-145/000-002</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow | <br><b>Item No.: 248-501/000-006</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue                                  | <br><b>Item No.: 248-501/000-007</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray                                    | <br><b>Item No.: 248-501/000-023</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green                                  |
| <br><b>Item No.: 248-501/000-017</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green                             | <br><b>Item No.: 248-501/000-012</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange                                | <br><b>Item No.: 248-501/000-005</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; red                                     | <br><b>Item No.: 248-501/000-024</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet                                 |
| <br><b>Item No.: 248-501</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white                                           | <br><b>Item No.: 248-501/000-002</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow                                |                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                         |

1.1.2.3 Marker carrier

|                                                                                                                                         |
|-----------------------------------------------------------------------------------------------------------------------------------------|
| <br><b>Item No.: 750-103</b><br>Group marker carrier |
|-----------------------------------------------------------------------------------------------------------------------------------------|

1.1.3 Shield termination

1.1.3.1 Shield clamping saddles

|                                                                                                                                                                                                      |                                                                                                                                                                     |                                                                                                                                                                                                      |                                                                                                                                                                        |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <br><b>Item No.: 790-108</b><br>Shield clamping saddle; 11 mm wide; diameter of compatible conductor; 3 ... 8 mm  | <br><b>Item No.: 790-208</b><br>Shield clamping saddle; 12.4 mm wide; 3 ... 8 mm | <br><b>Item No.: 790-116</b><br>Shield clamping saddle; 19 mm wide; diameter of compatible conductor; 7 ... 16 mm | <br><b>Item No.: 790-216</b><br>Shield clamping saddle; 21.8 mm wide; 6 ... 16 mm |
| <br><b>Item No.: 790-124</b><br>Shield clamping saddle; 27 mm wide; diameter of compatible conductor; 6 ... 24 mm | <br><b>Item No.: 790-220</b><br>Shield clamping saddle; 30 mm wide; 6 ... 20 mm  | <br><b>Item No.: 790-140</b><br>Shield clamping saddle; diameter of compatible conductor                          |                                                                                                                                                                        |



1.1.4 System enclosure

1.1.4.1 System enclosure



**Item No.: 850-825**  
IP65 enclosure; Aluminium (RAL 7032);  
WxHxD (160x100x160 mm); 9 x M12, 4 x  
M20



**Item No.: 850-826**  
IP65 enclosure; Aluminium (RAL 7032);  
WxHxD (240x100x160 mm); 4 x M20, 4 x  
M16, 14 x M12 cable grip



**Item No.: 850-827**  
IP65 enclosure; Aluminium (RAL 7032);  
WxHxD (320x100x160 mm); 4 x M20, 8 x  
M16, 17 x M12 cable grip



**Item No.: 850-828**  
IP65 enclosure; Aluminium (RAL 7032);  
WxHxD (480x100x160 mm); 4 x M20, 10 x  
M16, 35 x M12 cable grip



**Item No.: 850-826/002-000**  
IP65 enclosure; Aluminium (RAL 7035);  
WxHxD (240x100x160 mm); 4 x M20, 4 x  
M16, 14 x M12 cable grip



**Item No.: 850-827/002-000**  
IP65 enclosure; Aluminium (RAL 7035);  
WxHxD (320x100x160 mm); 4 x M20, 8 x  
M16, 17 x M12 cable grip



**Item No.: 850-828/002-000**  
IP65 enclosure; Aluminium (RAL 7035);  
WxHxD (480x100x160 mm); 4 x M20, 10 x  
M16, 35 x M12 cable grip



**Item No.: 850-834**  
IP65 enclosure; Polyester (RAL 7032); Wx-  
HxD (164x100x164 mm); 9 x M12, 4 x M20



**Item No.: 850-835**  
IP65 enclosure; Polyester (RAL 7032); Wx-  
HxD (244x100x164 mm); 4 x M20, 4 x  
M16, 14 x M12 cable grip



**Item No.: 850-836**  
IP65 enclosure; Polyester (RAL 7032);  
WxHxD (324x100x164 mm); 4 x M20, 8 x  
M16, 17 x M12 cable grip



**Item No.: 850-814/002-000**  
IP65 enclosure; Sheet steel (RAL 7035);  
WxHxD (200x120x200 mm); without flan-  
ge plate



**Item No.: 850-815/002-000**  
IP65 enclosure; Sheet steel (RAL 7035);  
WxHxD (300x120x200 mm); without flan-  
ge plate



**Item No.: 850-816/002-000**  
IP65 enclosure; Sheet steel (RAL 7035);  
WxHxD (400x120x200 mm); without flan-  
ge plate



**Item No.: 850-817/002-000**  
IP65 enclosure; Sheet steel (RAL 7035);  
WxHxD (600x120x200 mm); without flan-  
ge plate