





used for: D-SUB COMBINATION

NOTES:

- 1. MATERIAL: COPPER ALLOY
- 2. PLATING:
 - ITEM 1: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL
 - ITEM 2: min. 8µ" HARD GOLD OVER min. 50µ" NICKEL
 - ITEM 3: NICKEL PLATED

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACIION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACIION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
				ISO 2768-m		
				2002	date	name
				drawn	26.07.	Parei
				appd.	26.07.	E. Mickenbecker
				norm		
				d-old		
2 x c	Ä 1615	21.08.2002	Parei			
1 x b	Ä 1603	08.08.2002	Parei			
rev.	description	date	name			

scale:	5:1
material:	SEE NOTES
title:	
HIGH POWER CONTACT MALE	
(b) CRIMP / SOLDER VERSION 90° - 10A	
D-SUB COMBINATION	
dwg no:	AutoCAD
13K1A661	
part no:	131C16019X