

224MPW400K

GENERAL PURPOSE FILM

Parts are RoHS compliant

ic

ELECTRICAL SPECIFICATIONS

Capacitance: 0.22 μ F

Dissipation Factor: 0.001 Max at 1000 Hz and 25°C, 0.007 Max at 10 kHz and 25°C

Temperature Coefficient: -200 PPM/°C, -100 PPM/°C, 100 PPM/°C

Ripple Current: at and

ESR: 0.804 Ohms at 1 kHz and 20°C

Self Inductance: 1 Nanohenries maximum per mm of body length and lead length

dvd: 7.5 V/ μ s

Tolerance: -10 % , +10 %

Temperature Range: -55°C to +105°C

Above 85°C the rated (DC/AC) voltage must be derated at per 1.25%/°C

WVDC: 400 Volts DC

SVDC: N/A Volts DC

VAC: 220 Volts AC

Terminal to Terminal Dielectric strength: 1.6 times the rated DC voltage when applied between the terminals for 2 seconds

Terminal to case Dielectric strength: 2 VAC when applied between the terminals and case for 2~5 seconds

Insulation Resistance (Terminal to Terminal): 30000 MINIMUM after 100 Volts DC is applied for 60 seconds at 20°C

Reliability: 3 FIT

Load Life: 2000 hours at 85°C with 125% of rated voltage

Capacitance Change: $\leq$ 3% of initially measured value

D.F. Change: $\leq$ 125% of maximum specified value

I.R. Change: $>$ 50% of minimum specified value

Insulation resistance (Terminal to Case): N/A Megohms MINIMUM after 0 Volts DC is applied for 0 seconds at 0

PHYSICAL DIMENSIONS

Diameter (D): 10.5 mm, MAX mm


Length (L): 29 mm, MAX mm

Lead Finish: Matte Tin

Lead Spacing (S): mm, +/- mm

Lead Diameter (d): 0.8 mm, +/-0.05 mm

Lead Length (LL): 35mm, +/- MIN mm



2400 East Devon Avenue Suite 292 Des Plaines, IL 60018 (847) 675-1760 FAX (847) 673-2850

Illinois Capacitor (HK) Ltd., Tel: 85227930931, Fax: 85227930731, www.illcap.com.hk

© Copyright 2020 Illinois Capacitor. An affiliate of Cornell Dubilier, All Rights Reserved