SIEMENS

Data sheet 6ES7322-1BH01-0AA0



Figure similar

spare part SIMATIC S7-300, digital output SM 322, isolated, 16 DO, 24 V DC, 0.5 A, 1x 20-pole, total current 4 A/group (8 A/module)

Supply voltage	
Load voltage L+	
● Rated value (DC)	24 V
● permissible range, lower limit (DC)	20.4 V
● permissible range, upper limit (DC)	28.8 V
Input current	
from load voltage L+ (without load), max.	80 mA
from backplane bus 5 V DC, max.	80 mA
Power loss	
Power loss, typ.	4.9 W
Digital outputs	
Number of digital outputs	16
Short-circuit protection	Yes; Electronic
● Response threshold, typ.	1 A
Limitation of inductive shutdown voltage to	L+ (-53 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
● on lamp load, max.	5 W
Load resistance range	
● lower limit	48 Ω
● upper limit	4 kΩ
Output voltage	
● for signal "1", min.	L+ (-0.8 V)
Output current	
● for signal "1" rated value	0.5 A
● for signal "1" permissible range for 0 to 40 °C, min.	5 mA
● for signal "1" permissible range for 0 to 40 °C, max.	0.6 A
● for signal "1" permissible range for 40 to 60 °C, min.	5 mA
● for signal "1" permissible range for 40 to 60 °C, max.	0.6 A
● for signal "1" minimum load current	5 mA
● for signal "0" residual current, max.	0.5 mA
Output delay with resistive load	
● "0" to "1", max.	100 µs
● "1" to "0", max.	500 µs
Parallel switching of two outputs	
● for uprating	No
● for redundant control of a load	Yes
Switching frequency	

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

● with resistive load, max.	100 Hz
● with inductive load, max.	0.5 Hz
● with inductive load (acc. to IEC 60947-5-1, DC13), max.	0.5 Hz
● on lamp load, max.	10 Hz
Total current of the outputs (per group)	
horizontal installation	
— up to 40 °C, max.	4 A
— up to 60 °C, max.	3 A
vertical installation	
— up to 40 °C, max.	2 A
Cable length	
● shielded, max.	1 000 m
● unshielded, max.	600 m
Interrupts/diagnostics/status information	
Alarms	No
Diagnostics function	No
Alarms	
● Diagnostic alarm	No
Diagnoses	
● Wire break	No
● Short-circuit	No
● Fuse blown	No
● missing load voltage	No
Diagnostics indication LED	
● Rated load voltage PWR (green)	No
● Fuse OK FSG (green)	No
● Status indicator digital output (green)	Yes
Potential separation	
Potential separation digital outputs	
● between the channels	Yes
● between the channels, in groups of	8
● between the channels and backplane bus	Yes; Optocoupler
Isolation	
Isolation tested with	500 V DC
Connection method	
required front connector	20-pin
Dimensions	
Width	40 mm
Height	125 mm
Depth	120 mm
Weights	
Weight, approx.	190 g
Classifications	

	Version	Classification
eClass	14	27-24-22-04
eClass	12	27-24-22-04
eClass	9.1	27-24-22-04
eClass	9	27-24-22-04
eClass	8	27-24-22-04
eClass	7.1	27-24-22-04
eClass	6	27-24-22-04
ETIM	10	EC001419
ETIM	9	EC001419
ETIM	8	EC001419
ETIM	7	EC001419
IDEA	4	3566

© Copyright Siemens
Downloaded from Arrow.com.

	UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval




Manufacturer Declaration
Miscellaneous




General Product Approval


China RoHS
Manufacturer Declaration

EMV






For use in hazardous locations



FM




Miscellaneous


For use in hazardous locations

CCC-Ex

Maritime application









NK / Nippon Kaiji Kyokai

Maritime application





CCS (China Classification Society)

last modified: 4/7/2025

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.