




**PRODUCT NUMBER: 329-10-123-00-560000**

www.mill-max.com  
DATA SHEET



## General Info

**Description<sup>1</sup>:** Surface Mount Pin Header  
.018" (0,457mm) Pin Head

Type: Interconnect

**Category:** Machined Pin Header

**Mounting Style:** Surface Mount

# Pins: 23

**Packaging<sup>2</sup>:** Packaged in Box or Tube

Rows: Single Row

**ECCN:** Contact Factory

**HTSUS:** 8536.90.4040

## Product Lifecycle: Active

**Country Of Origin:** USA

# 329-10-123-00-560000- SPECIFICATIONS

Environmental Specs		Materials	
Temperature Range <sup>3</sup> :	-55/+125° C	Loose Pin/Receptacle # (Material):	2956 (Brass Alloy)
RoHS <sup>4</sup> :	Yes	Shell Plating:	10 $\mu$ " Gold over 100 $\mu$ " Nickel
Moisture Sensitivity Level (MSL):	1 (Unlimited)	Inner Plating:	
REACH Status:	REACH Unaffected	Insulator Material:	High Temp Thermoplastic
Technical Specs		Electrical Specs	
		Current Rating <sup>5</sup> :	Application Specific
		Rated Voltage:	100 VRMS/150 VDC
		Insulation Resistance:	10,000 M $\Omega$ min.
		Dielectric Withstanding Voltage:	1,000 VRMS min.

## NOTES:

### 1. Standard Tolerances

Assembly tolerance: +/- .010" (.25mm)

Connector Length "L"

Connector Length "L"	Tolerance
$L \leq 2"$ ( $L \leq 50.8$ mm)	+/- .005" (+/- .127 mm)
$2 < L \leq 3"$ ( $50.8 < L \leq 76.2$ mm)	+ .007 / - .006" (+ .178 / -.152 mm)
$3 < L \leq 4"$ ( $76.2 < L \leq 101.6$ mm)	+ .009 / - .007" (+ .229 / -.178 mm)
$4 < L \leq 5"$ ( $101.6 < L \leq 127$ mm)	+ .011 / - .008" (+ .279 / -.203 mm)
$5 < L \leq 6.4"$ ( $127 < L \leq 162.56$ mm)	+ .013 / - .009" (+ .330 / -.229 mm)

Insulator width: +/- .005 (.13mm)

Insulator height: +/- .005 (.13mm)

Co-planarity of SMT connectors: .005" (.13mm) up to 1" (25.4mm) in connector length

Insulator Flatness: .005" (.13mm) up to 1" (25.4mm) in connector length

Pin Length: +/- .005 (.13mm)

Pin Diameter: +/- .002 (.051mm)

Pin Angle: +/- 2°

2. Not all part numbers in the series may be packaged in tubes. Some specific part numbers may be packaged in a box.

3. Per IEC 60512-11-(4,-9,-10,-12)

4. Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).

5. Current rating is typically a measured function of the female socket/connector. The amount of current a solid, male, brass pin can tolerate is a direct relation of the heat displaced based on current and the ability of neighboring components to handle displaced heat.

## ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

## RELATED LINKS AND DOCUMENTS

- Engineering Notebook: [Introduction to Machined Pin PCB Connectors & Interconnects](#)
- Environmental Compliance: <https://www.mill-max.com/rohs>